


KEMET Part Number: ALF40C562EH100



ALF40, Aluminum Electrolytic, 105C, 5,600 uF, 20%, 100 VDC, -40/+105C



General Information

Supplier:	KEMET
Series:	ALF40
Dielectric:	Aluminum Electrolytic
Style:	Press-Fit
Description:	Press-Fit, Aluminum Electrolytic
RoHS:	Yes
Lead:	4 Pin Press-Fit
Notes:	Dimensions Include Sleeving
Shelf Life:	156 Weeks

Dimensions

D	40mm +1mm
L	60mm +/-2mm
S	22.5mm +/-0.1mm
LL	5.5mm +/-1mm
F	1.486mm +/-0.076mm

Packaging Specifications

Weight:	98 g
Packaging:	Bulk
Packaging Quantity:	36

Specifications

Capacitance:	5,600 uF
Capacitance Tolerance:	20%
Voltage DC:	100 VDC, 115 VDC (Surge)
Temperature Range:	-40/+105C
Rated Temperature:	105C
Life:	9000 Hrs (Rated Voltage And Ripple Current At 105C), 14000 Hrs (Rated Voltage At 105C)
Resistance:	49 mOhms (100Hz 20C), 42 mOhms (10kHz 20C)
Ripple Current:	7.46 Amps (100Hz 105C), 7.87 Amps (10kHz 105C)
Leakage Current:	1680 uA (5min 20C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006 - 2018 IntelliData.net