

OC25G16PNBN00NST44



Products → Low Voltage Products and Systems → Switches → Cam Switches

General Information

Extended Product Type:	OC25G16PNBN00NST44
Product ID:	1SCA138368R1001
EAN:	6417019667379
Catalog Description:	OC25G16PNBN00NST44 Cam switch
Long Description:	OC25 Cam switch, I _{th} =25A, Multi-Step, 16-contacts, Snap-on door mounting, Black Basic handle, Black handle and frontplate with standard text are included. Special engraved frontplates to be ordered as separate items.

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85365080

Popular Downloads

Data Sheet, Technical Information:	1SCC302009C0201
Instructions and Manuals:	1SCC302013F0006
Wiring Diagram:	1SCC302014M0201

Dimensions

Product Net Width:	51 mm
Product Net Height:	51 mm
Product Net Depth / Length:	167 mm
Product Net Weight:	0.25 kg

Technical

Rated Operational Current AC-22A (I_e):	(500 V) 20 A (690 V) 20 A
Conventional Free-air Thermal Current (I_{th}):	q = 40 °C 25 A
Conventional Thermal Current (I_{the}):	Fully Enclosed 25 A
Rated Continuous Thermal Current:	25 A
Rated Impulse Withstand Voltage (U_{imp}):	4 kV
Rated Insulation Voltage (U_i):	690 V
Rated Operational Voltage:	690 V

Rated Short-time Withstand Current (I_{cw}):	for 1 s 0.3 kA for 3 s 0.173 kA
Power Loss:	1.8 W
Pollution Degree:	3
Handle Type:	Basic handle
Special Functions:	Multistep switch: 4-step, without 0-position, step angle 30°, front plate 1-2-3-4
Color:	Black
Mounting Type:	Snap-on door mounting
Number of Contacts:	16
Number of Poles:	4
Terminal Type:	Screw Terminals

Technical UL/CSA

Ampere Rating UL/CSA: 600 V AC 25 A

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SCC302005D0201

Instructions and Manuals: 1SCC302013F0006

Container Information

Package Level 1 Units: 1 piece

Package Level 1 Width: 70 mm

Package Level 1 Depth / Length: 230 mm

Package Level 1 Height: 70 mm

Package Level 1 Gross Weight: 0.25 kg

Package Level 1 EAN: 6417019667379

Classifications

Object Classification Code: Q

ETIM 5: EC002611 - Control switch

ETIM 6: EC002611 - Control switch

ETIM 7: EC002611 - Control switch

