

www.lemo.com

# FGG.2T.319.CLAC85Z

# **SUMMARY**

#### # Wires

Fiber

 Low
 19

 High
 0

 Coax
 0

Triax 0

Quad 0

Fluidic 0

Series 2T

Termination type Male solder

IP rating 68

Cable Ø 8.10 - 8.50 mm

Matching parts EGG.2T.319.CLL

**Status** active

Alternative part



Image is for illustrative purpose only

### **Download**

Request a quote

Catalog

# **TECHNICAL DETAILS**

## **Mechanics**

Shell Style/Model FG\*: Straight plug, cable collet and nut for fitting a bend relief

**Keying** 1 keys (alpha=0; plug: male contacts, receptacle: female contacts)

Housing Material Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces

**Cable Fixing** C85: 8.1 - 8.5 mm

**Variant** Z: Nut for fitting a bend relief

Weight 30.56 g

#### **Performance**

Configuration T.319: 19 Low Voltage

Insulator

Rated Current 5 Amps

## **Specifications**

Contact Type: Solder

Vtest: 1250 V (DC)900 V (AC)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

### **Others**

Temp (min / max): -55°C / +200°C


Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms] Salt Spray Corrosion: >144 hr Climatical Category: 50/175/21 Shielding (min): 75 dB (10 MHz) Shielding (min): 40 dB (1 GHz)

IP Rating: 68

# **DRAWINGS**

### **Draws**







#### **Dimensions**

	А	L	М
mm.	15	54	42
in.	0,59	2,13	1,65

# **RECOMMENDED BY LEMO**

# Tools

None

#### **Cables**

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

