

# ESP MATV/F



ESP MATV/F Surge Protective Device

## General Information

Extended Product Type	ESP MATV/F
Product ID	7TCA085450R0000
EAN	5414363383451
Catalog Description	ESP MATV/F Surge Protective Device
Long Description	ESP MATV/F DATA SPD FOR MAIN ANTENNA TV MATV 5-2450MHZ WITH F TYPE CONNECTOR

## Ordering

EAN	5414363383451
Minimum Order Quantity	1 piece
Customs Tariff Number	8536301000

## Dimensions

Product Net Width	75 mm
Product Net Height	58 mm
Product Net Depth / Length	23 mm
Product Net Weight	0.14 kg

## Container Information

Package Level 1 Units	1 piece
Package Level 1 EAN	5414363383451

## Environmental

Ambient Air Temperature	Operation -40 ... +80 °C
-------------------------	--------------------------

## Additional Information

Connection Type	Push-in
Discharge Current	I (max, 8 / 20 $\mu$ s) 3 kA
Maximum Continuous Operating Voltage ( $U_c$ )	18.9 V
Nominal AC Voltage of the System ( $U_o$ )	18.9 V
Product Main Type	Data SPD

Product Name	Surge Protective Devices
Rated Current ( $I_n$ )	800 mA
Rated Frequency (f)	2450 MHz
Standards	IEC 61643-21
Suitable For	To protect systems against transient overvoltages or surges from lightning and electrical switching events
Voltage Protection Level (Up)	45 V

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	9AKK10103A0362
Declaration of Conformity - CE	9AKK106713A1078
Instructions and Manuals	9AKK106713A1369

### Classifications

ETIM 4	EC000943 - Surge protection device for data networks/MCR-technology
ETIM 5	EC000943 - Surge protection device for data networks/MCR-technology
ETIM 6	EC000943 - Surge protection device for data networks/MCR-technology

### Categories

Low Voltage Products and Systems → Surge Protective Devices → IEC/EN standard → Furse ESP specific systems protection

Low Voltage Products and Systems → Surge Protective Devices → IEC/EN standard → Furse special products

