

# 25 06 160 T

## Snipe Nose Side Cutting Pliers (Radio Pliers)


with tether attachment point



- Suitable for finer gripping and cutting work
- Half-round, long, tapered jaws
- Knurled gripping surfaces
- With cutting edges for soft, medium-hard and hard wire
- Cutting edges additionally induction hardened, cutting edge hardness approx. 61 HRC
- Vanadium electric steel, forged, multi stage oil-hardened
- Pliers with integrated, insulated tether attachment point for a tool tether



<b>Article No.</b>	25 06 160 T
<b>EAN</b>	4003773081432
<b>Pliers</b>	chrome plated
<b>Handles</b>	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
<b>Style</b>	0
<b>Head</b>	
<b>Insulation standard</b>	IEC 60900 DIN EN 60900
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	2,5
<b>Cutting capacities hard wire (diameter) Ø mm</b>	1,6
<b>T1 mm</b>	9,0
<b>W3 mm</b>	16,5
<b>W4 mm</b>	3,0
<b>T2 mm</b>	2,5
<b>L3 mm</b>	50,0
<b>Nominal size</b>	160 mm
<b>Length mm</b>	160
<b>Net weight g</b>	156



technical change and errors excepted