

# 95 12 200

## Cable Shears with twin cutting edge



**PATENTED**



- For cutting copper and aluminium cables
- Not suitable for steel wire and hard drawn copper conductors
- Precision ground, hardened blades
- Clean and smooth cut without crushing and deformation
- By dividing the cutting actions into initial cut (insulating sheath in the front cutting area) and final cut (conductor in the back cutting area), cables up to Ø 20 mm can be cut in one-hand operation
- Less effort required due to favourable lever ratio and optimised cutting-edge geometry
- Guard prevents operators' fingers being pinched
- Adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened

The twin cutting edge allows a comfortable handle position in all cutting situations within the specified cutting capacity.

<b>Article No.</b>	95 12 200
<b>EAN</b>	4003773047834
<b>Tool</b>	burnished
<b>Handles</b>	with multi-component grips
<b>Cutting capacity copper cable, multiple-stranded (diameter) Ø mm</b>	20
<b>Cutting capacity copper cable, multiple-stranded mm<sup>2</sup></b>	70
<b>AWG</b>	2/0
<b>Length mm</b>	200
<b>Net weight g</b>	324



Initial cut: using the front cutting edge to cut the insulating sheath on larger cable diameters leaves an ergonomic handle opening width.



Final cut: after cutting the sheath in the front profile the conductors in the rear part are cut. Initial cut in the front profile, final cut in the rear profile - to keep it as easy as possible.

technical change and errors excepted

