

**Industrial Ethernet
IE-XM-RJ45/IDC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Mounting rail outlet, RJ45 module design according to IEC 60603-7-51, for wires with diameters up to 1.6 mm

General ordering data

Type	IE-XM-RJ45/IDC
Order No.	8808360000
Version	Terminal rail outlet, RJ45 module EIA/TIA 568 A, RJ45 module EIA/TIA 568 B, IP20, Cat.6 _A / Class E _A (ISO/IEC 11801 2010)
GTIN (EAN)	4032248505944
Qty.	1 pc(s).

Industrial Ethernet IE-XM-RJ45/IDC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight 53 g

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-25 °C
Operating temperature	-25 °C...70 °C	Storage temperature	
Installation temperature			

General data

Connection 1	RJ45	Connection 2	IDC
Description of article		Configuration	Inspection window for labelling 1 TE pitch dimension acc. to DIN 43880. insta-compatible
	RJ45 module EIA/TIA 568 A, RJ45 module EIA/TIA 568 B		
Wiring	acc. to EIA/TIA 586-A, EIA/TIA T568 B	Colour	Light Grey
Housing main material	PA 66, UL 94: V-0	Insulation cross-section, min.	0.7 mm
Insulation cross-section, max.	1.6 mm	Category	Cat.6A / Class E _A (ISO/IEC 11801 2010)
Connection diameter, solid	0.4...0.64 mm	Conductor connection cross-section, solid (AWG)	AWG 26...AWG 22
Connection diameter, flexible	0.4...0.64 mm	Conductor connection cross-section, flexible (AWG)	AWG 26...AWG 22
Type of mounting	TS 35	Protection degree	IP20
Plugging cycles	750		

Electrical properties

Contact resistance	≤ 20 mΩ	Current-carrying capacity at 50 °C	1 A
Dielectric strength, contact / contact	≥ 1000 V DC	Dielectric strength, contact / shield	≥ 1500 V DC
Insulation resistance	500 MΩ	PoE / PoE+	conforming to IEEE 802.3at

Standards

Connector standard	IEC 60603-7-5	Certificate No. (GERMLLOYD)	33451-06
Certificate no. (cULus)	E316369		

Downloads

GL Approval Guidelines	GL_Certificate.pdf	GOST Approval	POCC DE.ME25.B01411.pdf
UL Approval	DUXR.E316369.pdf		

Classifications

ETIM 3.0	EC001264	ETIM 4.0	EC001264
ETIM 5.0	EC001264	ETIM 6.0	EC000313
UNSPSC	43-17-27-10	eClass 5.1	27-25-05-04
eClass 6.2	27-25-05-04	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	19-17-01-25
eClass 9.1	19-17-01-25		

Data sheet

**Industrial Ethernet
IE-XM-RJ45/IDC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Data sheet**Industrial Ethernet
IE-XM-RJ45/IDC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings**Dimensioned drawing**