

LED PAR30 & PAR30SN



11/12
watts

850/
950
lumens

up to
79
lpw

2700-
5000K
lpw

Features

- Direct replacement for halogen PARs
- Compatible with a wide array of dimmers
- +25,000 hour rated life for ENERGY STAR® Approved lamps*
- 50,000 hour design life**
- Up to 80% electricity savings vs. halogen
- Choice of 2700K, 3000K, 4000K and 5000K color temperatures
- ENERGY STAR® Approved
- 25° and 40° beam angles available
- No mercury or UV/IR emissions
- Shatter-resistant for reduced risk of injury and breakage



Performance

- 11W PAR30 replaces 75W PAR30 Halogen
- 11/12W PAR30SN replaces 75W PAR30SN Halogen
- 80+ CRI
- 120V @ 60Hz
- Operating temperature range from -40°F to 104°F (-40°C to 40°C)
- Not for use in enclosed fixtures
- Not for use with electronic timers, photocells, or motion/occupancy sensors
- Contains no mercury or lead; classified as non-hazardous waste

Applications

- Recessed / Track Lighting
- Property Management
- Accent / Display Lighting
- Retail / Residential
- Hospitality
- Houses of Worship
- Healthcare
- Task Lighting


* Early initial qualification for ENERGY STAR allows for directional lamp life claims of 25,000 hours (L70) with 3,000 hour actual test data, LM80 data and in-situ temperature measurements. As the lamps pass ENERGY STAR requirements, manufacturers may increase the lifetime of a product as dictated by ENERGY STAR guidelines. See http://www.energystar.gov/index.cfm?fuseaction=products_for_partners.showLightbulbs for further details.

** Design life is based on engineering testing and probability analysis



LED PAR30 & PAR30SN

Dimensions



Ordering Information

Order Code	Item #	Lm	W	CBCP	CCT	CRI	Bm	MOL	Life/Hrs*	Replaces Incandescent	ES v2.0
09993	LED11WPAR30/FL/827-DIM-G8	850	11W		2700K	80+	40°	4.57"	25K	75W PAR30	★
10070	LED11WPAR30/FL/830-DIM-G8	850	11W		3000K	80+	40°	4.57"	25K	75W PAR30	★
10071	LED11WPAR30/FL/840-DIM-G8	850	11W		4000K	80+	40°	4.57"	25K	75W PAR30	★
09994	LED11WPAR30/FL/850-DIM-G8	850	11W		5000K	80+	40°	4.57"	25K	75W PAR30	★
10072	LED11WPAR30/NFL/827-DIM-G8	850	11W		2700K	80+	25°	4.57"	25K	75W PAR30	★
10073	LED11WPAR30/NFL/830-DIM-G8	850	11W		3000K	80+	25°	4.57"	25K	75W PAR30	★
10074	LED11WPAR30/NFL/840-DIM-G8	850	11W		4000K	80+	25°	4.57"	25K	75W PAR30	★
09155	LED11WPAR30/FL/827K-DIM-G6	850	11W	2406	2700K	80+	40°	4.57"	25K	75W PAR30	★
09156	LED11WPAR30/FL/830K-DIM-G6	850	11W	1825	3000K	80+	40°	4.57"	25K	75W PAR30	★
09157	LED11WPAR30/FL/840K-DIM-G6	850	11W	2108	4000K	80+	40°	4.57"	25K	75W PAR30	★
09325	LED11WPAR30/FL/850K-DIM-G6	850	11W		5000K	80+	40°	4.57"	25K	75W PAR30	★
09158	LED11WPAR30/NFL/827K-DIM-G6	850	11W	2731	2700K	80+	25°	4.57"	25K	75W PAR30	★
09159	LED11WPAR30/NFL/830K-DIM-G6	850	11W	3452	3000K	80+	25°	4.57"	25K	75W PAR30	★
09160	LED11WPAR30/NFL/840K-DIM-G6	850	11W	4190	4000K	80+	25°	4.57"	25K	75W PAR30	★
10075	LED11WPAR30S/FL/827-DIM-G8	850	11W		2700K	80+	40°	3.62"	25K	75W PAR30	★
10076	LED11WPAR30S/FL/830-DIM-G8	850	11W		3000K	80+	40°	3.62"	25K	75W PAR30	★
10077	LED11WPAR30S/FL/840-DIM-G8	850	11W		4000K	80+	40°	3.62"	25K	75W PAR30	★
10078	LED11WPAR30S/NFL/827-DIM-G8	850	11W		2700K	80+	25°	3.62"	25K	75W PAR30	★
10079	LED11WPAR30S/NFL/830-DIM-G8	850	11W		3000K	80+	25°	3.62"	25K	75W PAR30	★
10080	LED11WPAR30S/NFL/840-DIM-G8	850	11W		4000K	80+	25°	3.62"	25K	75W PAR30	★
09480	LED12WPAR30S/NFL/830-DIM-G7	950	12W		3000K	80+	25°	3.62"	25K	75W PAR30	★
09481	LED12WPAR30S/NFL/840-DIM-G7	950	12W		4000K	80+	25°	3.62"	25K	75W PAR30	★
08557	LED12WPAR30S/NFL/830-DIM-G4A	850	12W	3,826	3000K	80+	25°	3.62"	25K	75W PAR30	
08558	LED12WPAR30S/NFL/840-DIM-G4A	850	12W	4,501	4000K	80+	25°	3.62"	25K	75W PAR30	
09476	LED12WPAR30S/FL/827-DIM-G7	950	12W		2700K	80+	40°	3.62"	25K	75W PAR30	★
09477	LED12WPAR30S/FL/830-DIM-G7	950	12W		3000K	80+	40°	3.62"	25K	75W PAR30	★
09478	LED12WPAR30S/FL/840-DIM-G7	950	12W		4000K	80+	40°	3.62"	25K	75W PAR30	★
09479	LED12WPAR30S/NFL/827-DIM-G7	950	12W		2700K	80+	25°	3.62"	25K	75W PAR30	★
09480	LED12WPAR30S/NFL/830-DIM-G7	950	12W		3000K	80+	25°	3.62"	25K	75W PAR30	★
09481	LED12WPAR30S/NFL/840-DIM-G7	950	12W		4000K	80+	25°	3.62"	25K	75W PAR30	★

NOTE: Use order code when ordering.

* 25,000 hour ENERGY STAR® rated life. 50,000 hour design life. See note on obverse.

★ ENERGY STAR® Approved

watch > like > follow



23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 · (F) 1.800.492.8975
 Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 · (F) 1.888.705.1335