

# **PX900D**

A low viscosity unfilled epoxy resin system

#### **Application**

- Castings
- · Impregnating and laminating
- Coils

#### **Key Properties**

- Low viscosity
- Long pot life
- Excellent Insulation characteristics
- Excellent long-term heat resistance
- Excellent chemical resistance

# Description

Basic Two-component epoxy system

Resin RX900DHardener HX900D

Physical Data (approx. – values)			
	Resin	Hardener	Mixed
Colour	Clear	Amber	Clear
Colour	Black	Amber	Black
Specific Gravity	1.17	0.94	1.14
Viscosity (mPas) @ 25°C	1200	50	650

Cure Schedule (150ml	sample)			
Temperature	Working Life (minutes)	Gel Time (minutes)	Light Handling (hours)	Full Cure (hours)
RT	150	360	36	72
60°C	40	-	4	8
80°C	10	-	2	4

<sup>\*</sup>RT is defined as 20-25°C

The above are typical values and will vary depending on the cured mass and application. Hotter temperatures may be used for faster cure but will result in higher post cure shrinkage and higher cure exotherm. Experimentation and testing is suggested to avoid side effects. For maximum properties a post cure may be required – Contact our technical service department for advice.

# Processing

Mix ratio by weight 100:38
Mix ratio by volume 100:47

Typical Properties		
Test	Result	Unit
Peak Exotherm (150ml @ 25°C)	40	°C
Shrinkage (volume)	0.6	%
Thermal Conductivity	0.21	W/mK
Thermal expansion	65-75	
Operating Temperature	- 62 to + 180	°C (Application and geometry dependant)
Electric Strength	22	kV/mm
Volume Resistivity	10 x 10 <sup>13</sup>	ohm.cm
Hardness	90	Shore D
Tensile strength	85	MPa
Compressive strength	120	MPa
Flexural Strength	120 - 140	MPa
Deflection temperature	140	°C
Coefficient Linear Expansion	65 – 75	ppm/°C
Loss Tangent	0.019	1kHz
Permittivity	3.9	1kHz
Comparative tracking index	>850	V
Water Absorption (30 days @ 20°C)	0.4	%
Elongation at break	1-3	%
Tg	120-140	°C

1

Approvals	
RoHS compliant	Yes
UL94 V-0	No
REACH (SVHC concentration)	0%

#### Packaging

PX900D is available in Bulk, Twinpacks & kits

#### Availability

Available through distribution and www.resins-online.com sales@robnor.co.uk

Cartridge Mixing – Part Numbers	
Not available	

It is essential for best results that the cartridge is 'balanced' before use to ensure correct mixing.

Loading the cartridge into the gun before attaching the mixer element and pumping the gun to push a small amount of the contents forward will achieve this.

Wipe the excess from the cartridge tip and add the static mixer.

The cartridge is now ready for use.

Twinpacks – Part Numbers	
PX900D/BK/050	PX900D/NC/050
PX900D/BK/100	PX900D/NC/100
PX900D/BK/150	PX900D/NC/250
	PX900D/NC/500

Twinpacks are pre-weighed resin and hardener components contained in a tough flexible film, separated by a removable clip and

Once the clip and rail is removed the resin and hardener is thoroughly mixed within the bag and is immediately ready for use. Mixing will normally take ~ 2 minutes due to the viscosity; but pay special attention to the corners.

Twinpacks are ideal for small to medium production runs, prototyping and on-site or field use.

The twinpack weight/volume may also be tailored to a specific size on request.

For further details please visit www.robnor-resinlab.com

Bulk Materials – Part Numbers	
RX900D/BK/1KG	HX900D/NC/500G
	HX900D/NC/1KG

Both resin and hardener are supplied in 5kg, 25kg and 200ltr drums and fully evacuated and ready for use.

Care should be taken to ensure when mixing the resins air is not entrained in the mixture.

If this is unavoidable the mixed resin and hardener should be re-evacuated before dispensing.

The bulk resin and hardener materials can be dispensed from suitable dispensing machinery, details provided by Fluid Research on request.

Kits and Sets – Part Numbers	
PX900D/BK/1.4KGSET	PX900D/NC/1.4KGSET

Kits and Sets are provided in separate containers to the correct ratio.

In Kit form, pour the hardener into the larger resin container and use it as a mixing vessel.

Stir well using an appropriate mixer until homogeneous.

Note: Incomplete mixing will be characterised by erratic or partially incomplete cure even after extended time periods.

#### Cleaning

All equipment contaminated with mixed material should be cleaned before the material has hardened.

TS130 is a suitable non-flammable cleaning agent, although other solvents may be found suitable.

TS130 will also remove cured material provided it is allowed to soak for a number of hours.

# Storage and Shelf Life

Material stored in the original unopened containers under cool dry condition between 15° and 25°C will have a shelf life of at least two years.

Once used the containers must be kept sealed to prevent effects from water, air or contaminants.

#### **Health and Safety**

Epoxy resin systems may cause sensitisation by skin contact or inhalation may be corrosive, harmful or toxic.

It is therefore strongly recommended that skin and eye contact is avoided by the using of appropriate personal protective equipment such as gloves, safety glasses or goggles and overalls.

Wash any contamination from the skin immediately and thoroughly and do not eat, smoke or drink in the working vicinity.

Under normal working conditions a good source of ventilation is adequate, however if the material is heated, or where vapour levels are likely to exceed the occupational exposure limits appropriate respiratory protection must be worn.

Local exhaust ventilation (LEV) may be required especially for curing ovens or where large volumes of material are curing. The above is given as a guide only; please refer to RX/HX900D Health and Safety data or our Technical Service Department for individual/specific advice.

# Copyright & Warranty - Robnor Resinlab Limited

The results and information above does not constitute a specification and is given in good faith and without warranty. The information is derived from test/or extrapolations believed to be reliable and is quoted for guidance only. The product is offered for evaluation on the understanding the customer satisfies himself that the product is suitable for the intended application by proper evaluation and testing.

#### **Contact Details**

Robnor Resinlab Limited Tel: +44 (0) 1793 823741 31 Athena Avenue Fax: +44 (0) 1793 827033

**Elgin Industrial Estate** 

United Kingdom Buy Online: <u>www.resins-online.com</u> (UK only)