



Material - Safety - Data Sheet (MSDS)

for

Ansmann Lithium-Iron-Disulfide (Li-metal) Batteries

single cells and multi-cell battery packs

No.1

1/6

Date of issue: 2011 - 07 - 04
Revision no: 10
Revision date: 2018 - 08 - 24
Editor: Ansmann AG

The information contained within is provided as a service to our customers and for their information only. The information and recommendations set forth herein are made in good faith and are believed to be accurate at the date of preparation. ANSMANN AG makes no warranty expressed or implied.

1. Product and Supplier Identification

Product name: "ANSMANN EXTREME Lithium"; "ANSMANN INDUSTRIAL Lithium"
Designation: Lithium Metal Battery
Models / types: AA / FR6 / L91; AAA / FR03 / L92
Electrochemical system: Li-FeS₂ (Lithium-Iron-Disulfide)

Supplier:
Germany ANSMANN AG
Address: Industriestraße 10; 97959 Assamstadt; Germany
Phone / Fax: + 49 (0) 6294 42040 / + 49 (0) 6294 420444
Home / email: ansmann.de / info@ansmann.de

USA ANSMANN USA Corporation
Address: 1001 Lower Landing Rd. Ste 101; Blackwood, NJ08012; USA
Phone / Facsimile: +1 973 4395244 1012 / +1 973 2062006
email: USA@ansmann.de

United Kingdom ANSMANN UK LTD.
Address: Units 11-12, RO24, Harlow Business Park, Harlow, Essex. CM19 5QB. UK
Phone / Facsimile: +44 (0) 870 609 2233 / +44 (0) 870609 2234
email: UK@ansmann.de

Hong Kong ANSMANN Energy Int. LTD.
Address: Unit 3117-18, 31/F; Tower 1; Millenium City 1; No. 388 Kwun Tong Road; Kwun Tong, kowloon; Hong-Kong
hongkong@ansmann.de

China HuiZhou City ANSMANN Trading Co. LTD
Address: Da Lian Industrial Park, Rengtu Village Ruhu Town Huicheng District, 516169 Huizhou City Guangdong, China
china@ansmann.de

Sweden ANSMANN Nordic AB
Address: Victor Hasselblads Gata 11, 421 31 Västra Frölunda, Sweden
nordic@ansmann.de

France Ansmann Energy France
Address: 5, Place Copernic; Immeuble Boréal - Courcouronnes; F-91023 Evry Cedex; France
Phone / Facsimile: +33 (1) 60791479 / +33 (1) 60791555
email: france@ansmann.de

EMERGENCY CONTACT: For chemical emergency only (spill, leak, fire, exposure or accident)
call CHEMTREC at: 800-424-9300 within the USA and Canada
+1 703-527-3887 outside the USA and Canada
Non-emergency calls cannot be serviced at this number.

2. Hazards Identification

The Lithium-Iron-Disulfide batteries described in this MSDS are hermetically sealed units, which are not hazardous when used according to the recommendations of the manufacturer.
Under normal condition of use of the batteries, the electrode materials and the liquid electrolyte they contain are non-reactive provided the battery integrity is maintained.
Risk of exposure exists only in case of mechanical, electrical or thermal abuse. Thus the batteries should not short circuited, recharged, punctured, incinerated, crushed, immersed in water, force discharged or exposed to temperatures above the temperature range of the cell or battery.
In these cases there is risk of fire or explosion.



Material - Safety - Data Sheet (MSDS)

for
Ansmann Lithium-Iron-Disulfide (Li-metal) Batteries
single cells and multi-cell battery packs

No.1

2/6

3. Composition and Informations on Ingredients

Each cell consists of a hermetically sealed metallic container containing a number of chemicals and materials of construction of which the following could potentially be hazardous upon release.

Ingredient	Content	CAS No.	ACGIH (TLV)	OSHA (PEL)
Lithium-Aluminum Alloy (Li-Al)	4 - 6%	7439-93-2	none established	none established
Iron Disulfide (FeS ₂)	25 - 40%	1309-36-0	none established	none established
Propylene Carbonate (PC)	<5%	108-32-7	none established	none established
1,2-Dimethoxyethane (DME)	<5%	110-71-4	none established	none established
1,3-Dioxolane (DOL)	<10%	646-06-0	none established	none established
Lithium Perchlorate	<1%	7791-03-9	none established	none established
Graphite	1 - 3%	7782-42-5	5mg/m ³ TWA (respirable fraction) 15mg/m ³ TWA (total dust)	2mg/m ³ TWA (respirable fraction)
stainless steel (Fe)	30 - 40%	7439-89-6	-	-
Aluminum (Al)	2 - 5%	7429-90-5	10mg/m ³ (dust)	5mg/m ³ (smog)
Acetylene black	1 - 2%	1333-86-4	3.5mg/m ³ TWA (as carbon black)	3.5mg/m ³ TWA (as carbon black)
Polypropylene	2 - 5%	9003-07-0	none established	none established
Adhesive CMC	0.1 - 2%	9085-26-1	none established	none established
Adhesive SBR	0.1 - 2%	9003-55-8	none established	none established

Remark: The weight of metallic lithium per AA (FR6) cell is ≤ 0.9g
per AAA (FR03) cell is ≤ 0.45g

4. First Aid Measures

Inhalation: Provide fresh air. In severe cases obtain medical attention.

Skin Contact: Wash off skin thoroughly with water. Remove contaminated clothing and wash before re-use. In severe cases obtain medical attention.

Eye Contact: Irrigate thoroughly with water for at least 15 minutes. Lifting upper and lower lids, until no evidence of the chemical remains. Obtain medical attention.

Ingestion: Wash out mouth thoroughly with water. Do not induce vomiting or give food or drink. Seek medical attention immediately.

Further treatment: All cases of eye contamination, persistent skin irritation and casualties who have swallowed this substance or been affected by breathing its vapours should be seen by a doctor.

5. Fire Fighting Measures

CO₂ extinguishers or, even preferably, copious quantities of water or water-based foam, can be used to cool down burning Li-FeS₂ cells and batteries, as long as the extent of the fire has not progressed to the point that the lithium metal they contain is exposed (marked by deep red flames).

Do not use for this purpose sand, dry powder or soda ash, graphite powder or fire blankets.

Use only metal (Class D) extinguishers on raw lithium.

Extinguishing media Use water or CO₂ on burning Li-FeS₂ cells or batteries and class D fire extinguishing agent only on raw lithium.

6. Accidental Release Measures

Remove personnel from area until fumes dissipate. Do not breathe vapours or touch liquid with bare hands.

If the skin has come into contact with the electrolyte, it should be washed thoroughly with water.

Sand or earth should be used to absorb any exuded material. Seal leaking battery and contaminated absorbent material in plastic bag and dispose of as Special Waste in accordance with local regulations.



Material - Safety - Data Sheet (MSDS)

for

Ansmann Lithium-Iron-Disulfide (Li-metal) Batteries

single cells and multi-cell battery packs

No.1

3/6

7. Precautions for safe Handling and Use

Storage: Store in a cool (preferable below 30°C), well ventilated area, away from moisture, sources of heat, open flames, food and drink. Elevated temperatures can result in shortened battery life. Temperatures above 100°C may result in battery leakage and rupture. In locations that handle large quantities of lithium batteries, such as warehouses, lithium batteries should be isolated from unnecessary combustibles. Keep batteries in original packaging until use and do not jumble them.

Mechanical Containment: If potting or sealing the battery in an airtight or watertight container is required, consult Ansmann AG representative for precautionary suggestions. Do not obstruct safety release vents on batteries. Encapsulation of batteries will not allow cell venting and can cause high pressure rupture.

Handling: Accidental short circuit for a few seconds will not seriously affect the battery. Prolonged short-circuit will cause the battery to lose energy, generate significant heat and cause the safety vent release vent to open. Sources of short-circuits include jumbled batteries in bulk containers, metal jewelry, metal covered tables or metal belts used for assembly of batteries into devices. Damaging a lithium battery may result in an internal short circuit.

The contents of an open battery, including a vented battery, when exposed to water, may result in a fire and / or explosion. Crushed or damaged batteries may result in a fire.

If soldering or welding to the battery is required, consult your Ansmann representative for proper precautions to prevent seal damage or short-circuit.

Charging: Do not charge this batteries! This battery type is manufactured in a ready-to-use-state. It is not designed for recharging.

Recharging can cause battery leakage, or in some cases, can cause the safety release vent to open. Inadvertent charging can occur if a battery is installed backwards.

Disposal: Dispose in accordance with all applicable federal, state and local regulations.

8. Special Protection Information

Ventilation Requirements: Not necessary under normal conditions. Room ventilation may be required in areas where there are open or leaking batteries.

Respiratory Protection: Not necessary under normal conditions. Avoid exposure to electrolyte fumes from open or leaking battery. In all fire situations, use self-contained breathing apparatus



Eye Protection: Not necessary under normal conditions. Wear safety glasses with side shields if handling an open or leaking battery.



Hand Protection: Not necessary under normal conditions. Use neoprene or natural rubber gloves if handling an open or leaking battery



9. Physical and Chemical Properties

Appearance:	small round cylinders	Odour:	n/a
Vapour Density:	n/a	Vapour Pressure:	n/a
Boiling Point:	n/a	VOC Content:	n/a
Evaporation Rate:	n/a	Solubility in Water:	n/a
Specific Gravity:	not determined	pH:	not determined



Material - Safety - Data Sheet (MSDS)

for

Ansmann Lithium-Iron-Disulfide (Li-metal) Batteries
single cells and multi-cell battery packs

No.1

4/6

Ingredients:

- FeS₂ is a brass-coloured, odourless mineral powder
melting point: FeS₂ decomposes at 1193°C
- Lithium is a soft, silvery metal
- Electrolyte is an organic solvent, consisting of PC, DME, DOL, lithium perchlorate
this organic solvent is an odourless, colourless or light yellow liquid

10. Stability and Reactivity

Product is stable under conditions described in Section 7.

Conditions to avoid: Heat above 100° or incinerate. Deform. Mutilate. Crush. Pierce. Disassemble. Recharge. Short circuit. Expose over a long period to humid conditions.

Materials to avoid: Oxidising agents, alkalis, water. Avoid electrolyte contact with aluminium or zinc.

Hazardous decomposition products: Hydrogen sulfide gas; Sulfur dioxide gas; Corrosive lithium hydroxide fumes

11. Toxicological Information

Signs & symptoms: None, unless battery ruptures. In the event of exposure to internal contents, corrosive fumes will be very irritating to skin, eyes and mucous membranes. Overexposure can cause symptoms of non-fibrotic lung injury and membrane irritation.

Inhalation: Lung irritant

Skin contact: Skin irritant

Eye contact: Eye irritant

Ingestion: Tissue damage to throat and gastro-respiratory tract if swallowed

Medical conditions generally aggravated by exposure: In the event of exposure to internal contents, eczema, skin allergies, lung injuries, asthma and other respiratory disorders may occur.

12. Ecological Information

Mammalian effects: None known if used / disposed of correctly

Eco-toxicity: None known if used / disposed of correctly

Environmental fate: None known if used / disposed of correctly

13. Disposal Information

Do not incinerate, recharge, disassemble short, or subject cells to temperatures in excess of 100°C. Such abuse can result in loss of seal, leakage, and/or cell explosion. Dispose of in accordance with appropriate local regulations.

When properly used and disposed the battery does not present environmental hazard. The battery does not contain mercury, cadmium, or lead. Do not let internal components enter marine environment. Avoid release to waterways, wastewater or ground water.

USA: Batteries must be completely discharged prior to disposal and / or the terminals must be taped or capped to prevent short circuit. This product does not contain any materials listed by the United States EPA as requiring specific waste disposal requirements. When completely discharged it is not considered hazardous. Disposal of large quantities of lithium power cells may be subject to Federal, State, or Local regulations.

In the European Union, manufacturing, handling and disposal of batteries is regulated on the basis of the DIRECTIVE 2006/66/EC OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 6 September 2006 on batteries and accumulators and waste batteries and accumulators and repealing Directive 91/157/EEC. Customers find detailed information on disposal in their specific countries using the web site of the European Portable Batteries Association (http://www.epbaeurope.net/legislation_national.html)

Importers and users outside EU should consider the local laws and rules.



Material - Safety - Data Sheet (MSDS)

for
Ansmann Lithium-Iron-Disulfide (Li-metal) Batteries
single cells and multi-cell battery packs

No.1

5/6

14. Transport Information

ADR

UN-Number: 3090
description: Lithium metal batteries
class: 9

packaging order: P903
special provision: 188; 230; 310; 376; 377; 636
tunnel forbidden code: E

UN-Number: 3091
description: Lithium metal batteries contained in equipment / packed with equipment
class: 9

packaging order: P903
special provision: 188; 230; 310; 360; 376; 377; 636
tunnel forbidden code: E

IATA

UN-Number: 3090
description: Lithium metal batteries
class: 9

packaging order: 968
special provision: A88; A99; A154; A164; A183; A201; A206

UN-Number: 3091
description: Lithium metal batteries contained in equipment
class: 9

packaging order: 970
special provision: A48; A88; A99; A154; A164; A181; A185; 206

UN-Number: 3091
description: Lithium metal batteries packed with equipment
class: 9

packaging order: 969
special provision: A88; A99; A154; A164; A181; A185; A206

IMDG-Code

UN-Number: 3090
description: Lithium metal batteries
class: 9

packaging order: P903
special provision: 188; 230; 310; 376; 377; 384

UN-Number: 3091
description: Lithium metal batteries contained in equipment / packed with equipment
class: 9

packaging order: P903
special provision: 188; 230; 310; 360; 376; 377; 384



Material - Safety - Data Sheet (MSDS)

for

Ansmann Lithium-Iron-Disulfide (Li-metal) Batteries
single cells and multi-cell battery packs

No.1

6/6

Since 1st of January 2013 it is necessary to produce both, lithium cells and lithium batteries under an existing quality assurance program.

The quality assurance program is detailed in following parts of the international dangerous goods laws:

- ADR (2017): 2.2.9.1.7 (e)
- IATA (2018, 59th edition): 3.9.2.6 (e)
- IMDG-Code (Amendment 38-16): 2.9.4 (5.)

Ansmann hereby declare that all lithium cells and batteries of the Ansmann product range are produced according the above named quality assurance program.

15. Regulatory Information

Regulations specifically applicable to the product:

- ACGIH and OSHA: see exposure limits of the internal
- IATA / ICAO (air transportation): UN 3090 or UN 3091
- Transportation within the US-DOT, 49 Code of Federal Regulations
- REACH regulation (1907/2006/EC)

Duty to communicate information on substances in articles (REACH, Article 33):

The product contains the following substance of very high concern (SVHC) in concentrations above 0.1% w/w: DME (CAS 110-71-4): reason for inclusion in the European candidate list - Toxic for reproduction (REACH, Article 57c).

Risk Phrases

substance	Risk Phrases	
Lithium (Li)	R14 / R15	Reacts violently with water, liberating extremely flammable gases.
		Harmful in contact with skin.
	R21	Harmful if swallowed.
	R22	Causes burns.
	R35	Risk of serious damage to eye.
	R41	May cause sensitization by inhalation and skin contact.
R42 / 43		

Safety Phrases

Lithium (Li)	S2	Keep out of reach of children
	S8	Keep away from moisture
	S45	In case of incident, seek medical attention

16. Other Information

This information has been compiled from sources considered to be dependable and is, to the best of our knowledge and belief, accurate and reliable as of the date compiled. However, no representation, warranty (either expressed or implied) or guarantee is made to the accuracy, reliability or completeness of the information contained herein.

This information relates to the specific materials designated and may not be valid for such material used in combination with any other materials or in any process. It is the user's responsibility to satisfy himself as to the suitability and completeness of this information for his particular use.

Ansmann AG does not accept liability for any loss or damage that may occur, whether direct, indirect, incidental or consequential, from the use of this information. Ansmann AG does not offer warranty against patent infringement