



**Part Number: 9575**

Power-Limited Fire Protective, (2) 16 AWG Solid BC, PVC/PVC, Foil Shld, CMR

[Request Sample](#)

## Product Description

Two 16 AWG solid bare copper conductors, PVC insulation, Beldfoil shield® shield (100% coverage), PVC jacket.

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

| AWG | Stranding | Material         | No. of Conductors |
|-----|-----------|------------------|-------------------|
| 16  | Solid     | BC - Bare Copper | 2                 |

|                        |        |
|------------------------|--------|
| Conductor Count:       | 2      |
| Total Number of Pairs: | 1      |
| Conductor Size:        | 16 AWG |

#### Insulation

| Material                 | Nominal Wall Thickness |
|--------------------------|------------------------|
| PVC - Polyvinyl Chloride | 0.016 in               |

#### Color Chart

| Number | Color |
|--------|-------|
| 1      | Black |
| 2      | Red   |

#### Outer Shield Material

| Type | Material           | Material Trade Name | Coverage [%] | Drainwire Material | Drainwire AWG | Drainwire Construction n x D |
|------|--------------------|---------------------|--------------|--------------------|---------------|------------------------------|
| Tape | Aluminum/Polyester | Beldfoil® (Z-Fold®) | 100 %        | TC - Tinned Copper | 22            | 7x30 mm                      |

#### Outer Jacket Material

| Material                 | Nominal Diameter | Nominal Wall Thickness |
|--------------------------|------------------|------------------------|
| PVC - Polyvinyl Chloride | 0.241 in         | 0.036 in               |

### Electrical Characteristics

#### Conductor DCR

| Nominal Conductor DCR | Nominal Outer Shield DCR |
|-----------------------|--------------------------|
| 4.1 Ohm/1000ft        | 10.6 Ohm/1000ft          |

#### Capacitance

| Nom. Capacitance Conductor to Conductor | Nom. Capacitance Conductor to Other Conductor to Shield |
|---|---|
| 57.5 pF/ft                              | 103.5 pF/ft   |

|            |                           |
|------------|---------------------------|
| Shielding: | Foil(s) or Copper Tape(s) |
|------------|---------------------------|

#### Inductance

| Nominal Inductance |
|--------------------|
| 0.15 µH/ft         |

#### Current

| Max. Recommended Current [A] |
|------------------------------|
| 11 Amps per conductor @ 25°C |

## Voltage

### UL Voltage Rating

300 V RMS

## Temperature Range

|                       |                 |
|-----------------------|-----------------|
| UL Temp Rating:       | 105°C           |
| Operating Temp Range: | -40°C To +105°C |

## Mechanical Characteristics

|                             |               |
|-----------------------------|---------------|
| Bulk Cable Weight:          | 34 lbs/1000ft |
| Min Bend Radius/Minor Axis: | 2.5 in        |

## Standards

|                          |                                |
|--------------------------|--------------------------------|
| NEC Articles:            | 760                            |
| NEC/(UL) Specification:  | CMR, FPLR                      |
| CEC/C(UL) Specification: | FAS105                         |
| UL AWM Style:            | UL Style 2464 (300 V 80°C)     |
| CPR Euroclass:           | Eca                            |
| Other Specification:     | California State Fire Marshall |

## Applicable Environmental and Other Programs

|                                       |                               |
|---------------------------------------|-------------------------------|
| EU Directive 2000/53/EC (ELV):        | Yes                           |
| EU Directive 2003/96/EC (BFR):        | Yes                           |
| EU Directive 2011/65/EU (ROHS II):    | Yes                           |
| EU Directive 2012/19/EU (WEEE):       | Yes                           |
| EU Directive Compliance:              | EU Directive 2003/11/EC (BFR) |
| EU CE Mark:                           | Yes                           |
| EU RoHS Compliance Date (yyyy-mm-dd): | 2005-04-01                    |
| CA Prop 65 (CJ for Wire & Cable):     | Yes                           |
| MII Order #39 (China RoHS):           | Yes                           |

## Flammability, LSOH, Toxicity Testing

|                    |                       |
|--------------------|-----------------------|
| UL Flammability:   | UL1666 Vertical Shaft |
| CSA Flammability:  | FT4                   |
| UL voltage rating: | 300 V RMS             |

## Part Number

### Variants

| Item #        | Color | Footnote |
|---------------|-------|----------|
| 9575.00305    | Red   |          |
| 9575.00U305   | Red   |          |
| 9575 0025000  | Red   | C Z      |
| 9575 002U1000 | Red   |          |
| 9575 002U500  | Red   |          |
| 9575.00U999   | Red   |          |

|           |  |
|-----------|--|
| Footnote: | C - CRATE REEL PUT-UP.   |
| Footnote: | Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN. |

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.