

# SFH6700/6719 SFH6701/6711 SFH6702/6712 SFH6705

## Low Input Current Logic Gate Optocoupler

Preliminary Data Sheet

### FEATURES

- Data Rate 5 MBits/s (2.5 MBit/s over Temperature)
- Buffer
- Isolation Test Voltage, 2500 VAC<sub>RMS</sub> for 1 min.
- TTL, LSTTL and CMOS Compatible
- Internal Shield for Very High Common Mode Transient Immunity
- Wide Supply Voltage Range (4.5 to 15 V)
- Low Input Current (1.6 mA to 5 mA)
- Three State Output (SFH6700/19)
- Totem Pole Output (SFH6701/02/11/12)
- Open Collector Output (SFH6705)
- Specified from 0°C to 85°C

### APPLICATIONS

- Industrial Control
- Replace Pulse Transformers
- Routine Logic Interfacing
- Motion/Power Control
- High Speed Line Receiver
- Microprocessor System Interfaces
- Computer Peripheral Interfaces


### DESCRIPTION

The SFH67xx high speed optocoupler series consists of a GaAlAs infrared emitting diode, optically coupled with an integrated photodetector. The detector incorporates a Schmitt-Trigger stage for improved noise immunity. Using the Enable input, the output can be switched to the high ohmic state, which is necessary for data bus applications. A Faraday shield provides a common mode transient immunity of 1000 V/μs at V<sub>CM</sub>=50 V for SFH6700/01/02/05 and 2500 V/μs at V<sub>CM</sub>=400 V for SFH6711/12/19.

The SFH67xx uses an industry standard DIP8 package. With standard lead bending, creepage distance and clearance of ≥7 mm with lead bending options 6, 7, and 9 ≥8 mm are achieved.

### Truth Table SFH6701/11/02/12/05 (Positive Logic)

IR Diode	Output
on	H
off	L



### Truth Table SFH6700/19 (Positive Logic)

IR Diode	Enable	Output
on	H	Z
off	H	Z
on	L	H
off	L	L

## Maximum Ratings

Parameter	Sym.	Min.	Max.	Units
<b>Emitter</b>				
Reverse Voltage	$V_R$		3	V
DC Forward Current	$I_F$		10	mA
Surge Forward Current ( $t_p \leq 1 \mu s$ , 300 pulses/s)	$I_{FSM}$		1	A
Total Power Dissipation	$P_{tot}$		20	mW
<b>Detector</b>				
Supply Voltage	$V_{CC}$	-0.5	15	V
Three State Enable Voltage (SFH6700/19 only)	$V_{EN}$	-0.5	15	V
Output Voltage	$V_O$	-0.5	15	V
Average Output Current	$I_O$		25	mA
Total Power Dissipation	$P_{tot}$		100	mW
<b>Package</b>				
Storage Temperature Range	$T_{STG}$	-55	125	$^{\circ}C$
Ambient Temperature Range	$T_A$	-40	85	$^{\circ}C$
Lead Soldering Temperature ( $t=10$ sec.)	$T_S$		260	$^{\circ}C$
Isolation Test Voltage ( $t=1$ min.)	$V_{ISO}$	2500		VAC <sub>RMS</sub>
Pollution Degree			2	
Creepage Distance and Clearance	Standard Lead Bending	7		mm
	Options 6, 7, 9	8		
Comparative Tracking Index per DIN IEC112/ VDE 0303, part 1			175	400
Isolation Resistance	$V_{IO}=500$ V, $T_A=25^{\circ}C$	$R_{ISO}$	$10^{12}$	$\Omega$
	$V_{IO}=500$ V, $T_A=100^{\circ}C$		$10^{11}$	


## Recommended Operating Conditions

A 0.1  $\mu F$  bypass capacitor connected between pins 5 and 8 must be used.


Parameter	Symbol	Min.	Max.	Unit
Supply Voltage	$V_{CC}$	4.5	15	V
Enable Voltage High (SFH6700/19)	$V_{EH}$	2.0	15	V
Enable Voltage Low (SFH6700/19)	$V_{EL}$	0	0.8	V
Forward Input Current	$I_{Fon}$	1.6 <sup>(1)</sup>	5	mA
Forward Input Current	$I_{Foff}$	-	0.1	mA
Operating Temperature	$T_A$	0	85	$^{\circ}C$
Output Pull-up Resistor (SFH6705 only)	$R_L$	350	4k	$\Omega$
Fan Out (SFH6705 at $R_L=1$ K $\Omega$ )	N		16	LS TTL Loads

1. We recommend using a 2.2 mA to permit at least 20% CTR degradation guard band.


Figure 1. Schematics




SFH6700/19



SFH6701/11



SFH6702/12



SFH6705

## Characteristics

$0^{\circ}\text{C} \leq T_A \leq 85^{\circ}\text{C}$ ;  $4.5\text{ V} \leq V_{\text{CC}} \leq 15\text{ V}$ ;  $1.6\text{ mA} \leq I_{\text{Fon}} \leq 5\text{ mA}$ ;  $2.0 \leq V_{\text{EH}} \leq 15\text{ V}$ ;  $0 \leq V_{\text{EL}} \leq 0.8\text{ V}$ ;  $0\text{ mA} \leq I_{\text{Foff}} \leq 0.1\text{ mA}$

Typical values:  $T_A = 25^{\circ}\text{C}$ ;  $V_{\text{CC}} = 5\text{ V}$ ;  $I_{\text{Fon}} = 3\text{ mA}$  unless otherwise specified

Parameter	Sym.	Min.	Typ.	Max.	Unit	Test Condition	
<b>Emitter</b>							
Forward Voltage	$V_F$		1.6	1.75	V	$I_F = 5\text{ mA}$ , $T_A = 25^{\circ}\text{C}$	
				1.8	V	$I_F = 5\text{ mA}$	
Input Current Hysteresis	$I_{\text{HYS}}$		0.1		mA	$V_{\text{CC}} = 5\text{ V}$ , $I_{\text{HYS}} = I_{\text{Fon}} - I_{\text{Foff}}$	
Reverse Current	$I_R$		0.5	10	$\mu\text{A}$	$V_R = 3\text{ V}$ , $T_A = 25^{\circ}\text{C}$	
Capacitance	$C_0$		60		pF	$V_R = 0\text{ V}$ , $f = 1\text{ MHz}$ , $T_A = 25^{\circ}\text{C}$	
Thermal Resistance	$R_{\text{thJA}}$		700		K/W		
<b>Detector</b>							
Logic Low Output Voltage	$V_{\text{OL}}$			0.5	V	$I_{\text{OL}} = 6.4\text{ mA}$	
Logic High Output Voltage (except SFH6705)	$V_{\text{OH}}$	2.4	*		V	$I_{\text{OH}} = -2.6\text{ mA}$ , $*V_{\text{OH}} = V_{\text{CC}} - 1.8\text{ V}$	
Output Leakage Current ( $V_{\text{OUT}} > V_{\text{CC}}$ ) (except SFH6705)	$I_{\text{OHH}}$		0.5	100	$\mu\text{A}$	$V_O = 5.5\text{ V}$ , $V_{\text{CC}} = 4.5\text{ V}$ , $I_F = 5\text{ mA}$	
			1	500	$\mu\text{A}$	$V_O = 15\text{ V}$ , $V_{\text{CC}} = 4.5\text{ V}$ , $I_F = 5\text{ mA}$	
Output Leakage Current (SFH6705 only)	$I_{\text{OHH}}$		0.5	100	$\mu\text{A}$	$V_O = 5.5\text{ V}$ , $V_{\text{CC}} = 5.5\text{ V}$ , $I_F = 5\text{ mA}$	
			1	500	$\mu\text{A}$	$V_O = 15\text{ V}$ , $V_{\text{CC}} = 15\text{ V}$ , $I_F = 5\text{ mA}$	
Logic High Enable Voltage (SFH6700/19 only)	$V_{\text{EH}}$	2.0			V		
Logic Low Enable Voltage (SFH6700/19 only)	$V_{\text{EL}}$			0.8	V		
Logic High Enable Current (SFH6700/19 only)	$I_{\text{EH}}$			20	$\mu\text{A}$	$V_{\text{EN}} = 2.7\text{ V}$	
				100	$\mu\text{A}$	$V_{\text{EN}} = 5.5\text{ V}$	
			0.00 1	250	$\mu\text{A}$	$V_{\text{EN}} = 15\text{ V}$	
Logic Low Enable Current (SFH6700/19 only)	$I_{\text{EL}}$	-320	-50		$\mu\text{A}$	$V_{\text{EN}} = 0.4\text{ V}$	
High Impedance State Output Current (SFH6700/19 only)	$I_{\text{OZL}}$				$\mu\text{A}$	$V_O = 0.4\text{ V}$ , $V_{\text{EN}} = 2.0\text{ V}$ , $I_F = 5\text{ mA}$	
		$I_{\text{OZH}}$			20	$\mu\text{A}$	$V_O = 2.4\text{ V}$ , $V_{\text{EN}} = 2.0\text{ V}$ , $I_F = 0$
					100	$\mu\text{A}$	$V_O = 5.5\text{ V}$ , $V_{\text{EN}} = 2.0\text{ V}$ , $I_F = 0$
				0.00 1	500	$\mu\text{A}$	$V_O = 15\text{ V}$ , $V_{\text{EN}} = 2.0\text{ V}$ , $I_F = 0$
Logic Low Supply Current	$I_{\text{CCL}}$		3.7	6.0	mA	$V_{\text{CC}} = 5.5\text{ V}$ , $I_F = 0$	
			4.1	6.5	mA	$V_{\text{CC}} = 15\text{ V}$ , $I_F = 0$	
Logic High Supply Current	$I_{\text{CCH}}$		3.4	4.0	mA	$V_{\text{CC}} = 5.5\text{ V}$ , $I_F = 5\text{ mA}$	
			3.7	5.0	mA	$V_{\text{CC}} = 15\text{ V}$ , $I_F = 5\text{ mA}$	
Logic Low Short Circuit Output Current	$I_{\text{OSL}}^{(2)}$		25		mA	$V_O = V_{\text{CC}} = 5.5\text{ V}$ , $I_F = 0$	
			40		mA	$V_O = V_{\text{CC}} = 15\text{ V}$ , $I_F = 0$	
Logic High Short Circuit Output Current (except SFH6705)	$I_{\text{OSH}}^{(2)}$			-10	mA	$V_{\text{CC}} = 5.5\text{ V}$ , $V_O = 0\text{ V}$ , $I_F = 5\text{ mA}$	
				-25	mA	$V_{\text{CC}} = 15\text{ V}$ , $V_O = 0\text{ V}$ , $I_F = 5\text{ mA}$	
Thermal Resistance	$R_{\text{thJA}}$		300		K/W		
<b>Package</b>							
Coupling Capacitance	$C_{\text{IO}}$		0.6		pF	$f = 1\text{ MHz}$ , pins 1–4 and 5–8 shorted together	
Isolation Resistance	$R_{\text{ISO}}$		$10^{12}$		$\Omega$	$V_{\text{IO}} = 500\text{ V}$ , $T_A = 25^{\circ}\text{C}$	
			$10^{11}$		$\Omega$	$V_{\text{IO}} = 500\text{ V}$ , $T_A = 100^{\circ}\text{C}$	

2. Output short circuit time  $\leq 10\text{ ms}$ .

### Switching Times <sup>(3)</sup>

0°C ≤ T<sub>A</sub> ≤ 85°C; 4.5 V ≤ V<sub>CC</sub> ≤ 15 V; 1.6 mA ≤ I<sub>Fon</sub> ≤ 5 mA; 2.0 V ≤ V<sub>EH</sub> ≤ 15 V (SFH6700/19);

0 ≤ V<sub>EL</sub> ≤ 0.8 V (SFH6700/19); 0 mA ≤ I<sub>Foff</sub> ≤ 0.1 mA

Typical values: T<sub>A</sub> = 25°C; V<sub>CC</sub> = 5 V; I<sub>Fon</sub> = 3 mA unless otherwise specified

Parameter, SFH6700/01/02/11/12/19	Symbol	Min.	Typ.	Max.	Unit	Test Condition
Propagation Delay Time to Logic Low Output Level	t <sub>PHL</sub>		120		ns	Without Peaking Capacitor
			115	300		With Peaking Capacitor
Propagation Delay Time to Logic Low Output Level	t <sub>PLH</sub>		125		ns	Without Peaking Capacitor
			90	300		With Peaking Capacitor
Output Enable Time to Logic High (SFH6700/19)	t <sub>PZH</sub>		20		ns	
Output Enable Time to Logic Low (SFH6700/19)	t <sub>PZL</sub>		25		ns	
Output Disable Time from Logic High (SFH6700/19)	t <sub>PHZ</sub>		50		ns	
Output Disable Time from Logic Low (SFH6700/19)	t <sub>PLZ</sub>		50		ns	
Output Rise Time	t <sub>r</sub>		40		ns	10% to 90%
Output Fall Time	t <sub>f</sub>		10		ns	90% to 10%

### Switching Times <sup>(3)</sup>

Typical values: T<sub>A</sub> = 25°C, V<sub>CC</sub> = 5 V; I<sub>Fon</sub> = 3 mA, R<sub>L</sub> = 390 Ω, unless otherwise specified

Parameter, SFH6705	Symbol	Min.	Typ.	Max.	Unit	Test Condition
Propagation Delay Time to Logic Low Output Level	t <sub>PHL</sub>		115		ns	Without Peaking Capacitor
			105	300		With Peaking Capacitor
Propagation Delay Time to Logic Low Output Level	t <sub>PLH</sub>		125		ns	Without Peaking Capacitor
			90	300		With Peaking Capacitor
Output Rise Time	t <sub>r</sub>		25		ns	10% to 90%
Output Fall Time	t <sub>f</sub>		4		ns	90% to 10%

### Common Mode Transient Immunity T<sub>A</sub> = 25°C, V<sub>CC</sub> = 5 V<sup>(4)</sup>

Parameter	Device	Symbol	Min.	Unit	Test Condition
Logic High Common Mode Transient Immunity	SFH6700/01/02/05	CM <sub>H</sub>   <sup>(4)</sup>	1000	V/μs	V <sub>CM</sub>   = 50 V, I <sub>F</sub> = 1.6 mA
	SFH6711/12/19		2500	V/μs	V <sub>CM</sub>   = 400 V, I <sub>F</sub> = 1.6 mA
Logic Low Common Mode Transient Immunity	SFH6700/01/02/05	CM <sub>L</sub>   <sup>(4)</sup>	1000	V/μs	V <sub>CM</sub>   = 50 V, I <sub>F</sub> = 0
	SFH6711/12/19		2500	V/μs	V <sub>CM</sub>   = 400 V, I <sub>F</sub> = 0

3. A 0.1 μF bypass capacitor connected between pins 5 and 8 must be used.

4. CM<sub>H</sub> is the maximum slew rate of a common mode voltage V<sub>CM</sub> at which the output voltage remains at logic high level (V<sub>O</sub> > 2 V).

CM<sub>L</sub> is the maximum slew rate of a common mode voltage V<sub>CM</sub> at which the output voltage remains at logic low level (V<sub>O</sub> < 0.8 V).

Figure 2. Permissible total power dissipation vs. temperature




Figure 3. Typical input diode forward current vs. forward voltage




Figure 4. Typical forward input voltage vs. temperature




Figure 8. Typical output leakage current vs. temperature




Figure 5. Typical output voltage vs. forward input current (except SFH6705)




Figure 9. Typical low level output current vs. temperature




Figure 6. Typical output forward voltage vs. forward input current (only SFH6705)




Figure 10. Typical low level output voltage vs. temperature




Figure 7. Typical supply current vs. temperature







Figure 11. Typical high level output current vs. temperature (except SFH6705)




**Figure 12. Typical rise, fall time vs. temperature (except SFH6705)**




**Figure 16. Typical propagation delays to logic low vs. temperature**




**Figure 13. Typical propagation delays to logic high vs. temperature (except SFH6705)**




**Figure 17. Typical propagation delays to logic high vs. temperature**




**Figure 14. Typical propagation delays to logic low vs. temperature (except SFH6705)**




**Figure 18. Typical propagation delays to logic low vs. temperature**




**Figure 15. Typical propagation delays to logic high vs. temperature (except SFH6705)**




**Figure 19. Typical propagation delays to logic high vs. temperature**




**Figure 20. Typical propagation delays to logic low vs. temperature (except SFH6705)**




**Figure 21. Typical logic low enable propagation delays vs. temperature (only SFH6700/11)**




**Figure 22. Typical logic high enable propagation delays vs. temperature (only SFH6700/11)**




**Figure 23. Typical propagation delays vs. pulse Input current (only SFH6705)**




**Figure 24. Typical propagation delays to high level vs. temperature (only SFH 6705)**




**Figure 25. Typical propagation delays to low level vs. temperature (only SFH 6705)**



**Figure 26. Typical rise, fall time vs. temperature (only SFH6705)**




**Figure 27. Test circuit for  $t_{PLH}$ ,  $t_{PHL}$ ,  $t_r$  and  $t_f$ —SFH6700/01/02/11/12/19**




The Probe and Jig Capacitances are included in C1 and C2 All diodes are 1N916 or 1N3064

R1	2.15 kOhm	1.1 kOhm	681 Ohm
$I_F$ (ON)	1.6 mA	3 mA	5 mA

\* SFH6701/02/11/12 without  $V_{EN}$   
\* SFH6702/12 Pin 6  $V_{OUT}$  and Pin 7 n.c.




**Figure 28. Test circuit for  $t_{PLH}$ ,  $t_{PHL}$ ,  $t_r$  and  $t_f$ —SFH6705**





The Probe and Jig Capacitances are included in C1 and C2

R1	2.15 kOhm	1.1 kOhm	681 Ohm
$I_F$ (ON)	1.6 mA	3 mA	5 mA






**Figure 29. Test circuit for  $t_{PHZ}$ ,  $t_{PZH}$ ,  $t_{PLZ}$  and  $t_{PZL}$ —SFH6700/19**




**Figure 30. Test circuit for common mode transient immunity and typical waveforms—SFH 6700/01/02/11/12/19**



\* SFH6701/02/11/12 without  $V_{EN}$

\* SFH6702/12 Pin 6  $V_{OUT}$  and Pin 7 n.c.



**Figure 31. Test circuit for common mode transient immunity and typical waveforms—SFH6705<sub>L</sub>**

