



Main

Range	TeSys
Product name	TeSys LRD
Product or component type	Differential thermal overload relay
Device short name	LRD
Relay application	Motor protection
Product compatibility	LC1D80 LC1D95
Network type	AC DC
Thermal protection adjustment range	48...65 A
[Ui] rated insulation voltage	1000 V power circuit conforming to IEC 60947-4-1 600 V power circuit conforming to CSA 600 V power circuit conforming to UL

Complementary

Network frequency	0...400 Hz
Mounting support	Plate with specific accessories Rail with specific accessories Under contactor
Tripping threshold	1.14 +/- 0.06 I _r conforming to IEC 60947-4-1
[I _{th}] conventional free air thermal current	5 A for signalling circuit
Permissible current	0.72 A at 500 V AC-15 for signalling circuit 0.06 A at 440 V DC-13 for signalling circuit
[U _e] rated operational voltage	690 V AC 0...400 Hz
[U _{imp}] rated impulse withstand voltage	6 kV
Phase failure sensitivity	Tripping current 130 % of I _r on two phase, the last one at 0
Control type	Red push-button stop Blue push-button for reset mode
Temperature compensation	-20...60 °C

Connections - terminals	Power circuit : screw clamp terminals 1 cable(s) 4...35 mm ² flexible without cable end Power circuit : screw clamp terminals 1 cable(s) 4...35 mm ² flexible with cable end Power circuit : screw clamp terminals 1 cable(s) 4...35 mm ² solid without cable end Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible without cable end Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² flexible with cable end Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² solid without cable end
Tightening torque	Control circuit : 1.7 N.m on screw clamp terminals Power circuit : 9 N.m on screw clamp terminals
Height	123 mm
Width	75 mm
Depth	121 mm
Product weight	0.51 kg

Environment

Protective treatment	TH conforming to IEC 60068
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	Without derating conforming to IEC 60947-4-1
Ambient air temperature for storage	-60...70 °C
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Vibrations 6 Gn IEC 60068-2-6 Shocks 15 Gn for 11 ms IEC 60068-2-7
Dielectric strength	6 kV at 50 Hz conforming to IEC 60255-5
Standards	ATEX D 94/9/CE EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 CSA C22.2 No 14
Product certifications	ATEX INERIS BV CCC CSA DNV GL GOST LROS (Lloyds register of shipping) RINA UL

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0849 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product environmental
Product end of life instructions	Available End of life manual

Contractual warranty

Warranty period	18 months
-----------------	-----------