

# Crimp Information Sheet

Terminal Part Number: 15326266  
 Surface Plating: SN  
 Material Thickness [mm]: 0,30  
 Cross Section [mm<sup>2</sup>]: 0,35 | 0,50

*This document is non-contractual  
 and for information only.  
 For more information, please  
 consult your local sales office*



Cable Type codes: 1005  
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY  
 Insulation Range  $\Phi$ [mm]: 1,45 - 1,88  
 Seal(s): 15366022

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1005 0,35 / 15366022		1,60	55	1,05	0,05	1,80	0,10	2,80	0,10	3,00	0,10
1005 0,50 / 15366022		1,74	80	1,10	0,05	1,80	0,10	2,90	0,10	3,00	0,10

Cable type code legend:

1005:

Industry Designator: SAE  
 Conductor Material: COPPER  
 Conductor Plating: NONE  
 Insul. Material: PVC, PVDF, XLPE  
 Insul. Wall Designator: THIN



# Crimp Information Sheet

Terminal Part Number: 15326266  
 Surface Plating: SN  
 Material Thickness [mm]: 0,30  
 Cross Section [mm<sup>2</sup>]: 0,50

*This document is non-contractual  
 and for information only.  
 For more information, please  
 consult your local sales office*



Cable Type codes: 1007  
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY  
 Insulation Range  $\Phi$ [mm]: 2,00 - 2,30  
 Seal(s): 15305351

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1007 0,50 / 15305351		2,15	80	1,10	0,05	1,80	0,10	3,50	0,10	3,00	0,10

## Cable type code legend:

1007:

Industry Designator: SAE  
 Conductor Material: COPPER  
 Conductor Plating: NONE  
 Insul. Material: PVC, XLPA/PVDF, XLPE  
 Insul. Wall Designator: REGULAR



# Crimp Information Sheet

Terminal Part Number: 15326266  
 Surface Plating: SN  
 Material Thickness [mm]: 0,30  
 Cross Section [mm<sup>2</sup>]: 0,35 | 0,50

*This document is non-contractual  
 and for information only.  
 For more information, please  
 consult your local sales office*



Cable Type codes: 1025  
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY  
 Insulation Range  $\Phi$ [mm]: 1,47 - 1,85  
 Seal(s): 15366022

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1025 0,35 / 15366022		1,55	55	1,05	0,05	1,80	0,10	2,80	0,10	3,00	0,10
1025 0,50 / 15366022		1,73	80	1,10	0,05	1,80	0,10	2,90	0,10	3,00	0,10

Cable type code legend:

1025:

Industry Designator: SAE  
 Conductor Material: COPPER  
 Conductor Plating: SN  
 Insul. Material: FLUORPOLYM, HDPE, PBT, PE, PVC, XLPE  
 Insul. Wall Designator: THIN



# Crimp Information Sheet

Terminal Part Number: 15326266  
 Surface Plating: SN  
 Material Thickness [mm]: 0,30  
 Cross Section [mm<sup>2</sup>]: 0,35

*This document is non-contractual  
 and for information only.  
 For more information, please  
 consult your local sales office*



Cable Type codes: 1047  
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY  
 Insulation Range  $\Phi$ [mm]: 1,40 - 1,75  
 Seal(s): 15366022

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1047 0,35 / 15366022		1,58	70	1,05	0,05	1,80	0,10	2,80	0,10	3,00	0,10

## Cable type code legend:

1047:

Industry Designator: SAE  
 Conductor Material: COPPER  
 Conductor Plating: NONE  
 Insul. Material: PVC, XLPE  
 Insul. Wall Designator: THIN



# Crimp Information Sheet

Terminal Part Number: 15326266  
 Surface Plating: SN  
 Material Thickness [mm]: 0,30  
 Cross Section [mm<sup>2</sup>]: 0,35 | 0,50 | 0,60 | 1,00

*This document is non-contractual  
 and for information only.*

*For more information, please  
 consult your local sales office*



Cable Type codes: 2010  
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY  
 Insulation Range  $\Phi$ [mm]: 1,20 - 2,10  
 Seal(s): 12191226 | 15366022 | 12191229 | 15344324

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 0,35 / 15366022		1,34	50	1,15	0,05	1,65	0,10	3,00	0,10	3,00	0,10
2010 0,35 / 12191229		1,34	50	1,15	0,05	1,65	0,10	3,00	0,10	3,00	0,10
2010 0,35 / 15344324		1,34	50	1,15	0,05	1,65	0,10	3,00	0,10	3,00	0,10
2010 0,35 / 12191226		1,34	50	1,15	0,05	1,65	0,10	3,00	0,10	3,00	0,10
2010 0,50 / 12191226		1,50	80	1,25	0,05	1,65	0,10	3,10	0,10	3,00	0,10
2010 0,50 / 15366022		1,50	80	1,25	0,05	1,65	0,10	3,10	0,10	3,00	0,10
2010 0,50 / 12191229		1,50	80	1,25	0,05	1,65	0,10	3,10	0,10	3,00	0,10
2010 0,50 / 15344324		1,50	80	1,25	0,05	1,65	0,10	3,10	0,10	3,00	0,10
2010 0,60 / 12191229		1,83	100	1,20	0,05	1,70	0,10	3,20	0,10	3,10	0,10
2010 1,00 / 15344324		1,95	178	1,10	0,05	1,90	0,10	3,05	0,10	2,80	0,10

## Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR (AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B

Industry Designator: DIN  
 Conductor Material: COPPER  
 Conductor Plating: NONE  
 Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE, XLPE/PVDF, XLPVC  
 Insul. Wall Designator: THIN



# Crimp Information Sheet

Terminal Part Number: 15326266  
 Surface Plating: SN  
 Material Thickness [mm]: 0,30  
 Cross Section [mm<sup>2</sup>]: 0,35



*This document is non-contractual  
 and for information only.  
 For more information, please  
 consult your local sales office*

Cable Type codes: 2011  
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY  
 Insulation Range  $\Phi$ [mm]: 1,79 - 2,10  
 Seal(s): 15305351

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2011 0,35 / 15305351		1,95	50	1,05	0,05	1,80	0,10	2,60	0,10	3,00	0,10

## Cable type code legend:

2011: FL33X, FLK, FLY, FLYKW, IH WIRE  
 Industry Designator: DIN  
 Conductor Material: COPPER  
 Conductor Plating: NONE  
 Insul. Material: P/EST, PE, PVC, XLPE  
 Insul. Wall Designator: REGULAR



# Crimp Information Sheet

Terminal Part Number: 15326266  
 Surface Plating: SN  
 Material Thickness [mm]: 0,30  
 Cross Section [mm<sup>2</sup>]: 0,50



*This document is non-contractual  
 and for information only.  
 For more information, please  
 consult your local sales office*

Cable Type codes: 2019  
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY  
 Insulation Range  $\Phi$ [mm]: 1,30 - 1,70  
 Seal(s): 15344324

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2019 0,50 / 15344324		1,50	75	1,10	0,05	1,90	0,10	3,00	0,10	2,85	0,10

## Cable type code legend:

2019: FL7Y 179, FLR7Y, FLR7Y-A, FLR7Y-B, FLU7Y  
 Industry Designator: DIN  
 Conductor Material: COPPER  
 Conductor Plating: SN  
 Insul. Material: ETFE  
 Insul. Wall Designator: THIN



# Crimp Information Sheet

Terminal Part Number: 15326266  
 Surface Plating: SN  
 Material Thickness [mm]: 0,30  
 Cross Section [mm<sup>2</sup>]: 0,50

*This document is non-contractual  
 and for information only.  
 For more information, please  
 consult your local sales office*



Cable Type codes: 2041  
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY  
 Insulation Range  $\Phi$ [mm]: 1,43 - 1,61  
 Seal(s): 15366022

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2041 0,50 / 15366022		1,52	75	1,15	0,05	1,80	0,10	3,10	0,10	3,00	0,10

## Cable type code legend:

2041:

Industry Designator: ISO  
 Conductor Material: COPPER  
 Conductor Plating: NONE  
 Insul. Material: PPE  
 Insul. Wall Designator: THIN





# Crimp Information Sheet

Terminal Part Number: 15326266  
 Surface Plating: SN  
 Material Thickness [mm]: 0,30  
 Cross Section [mm<sup>2</sup>]: 0,50

*This document is non-contractual  
 and for information only.  
 For more information, please  
 consult your local sales office*



Cable Type codes: 2083  
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY  
 Insulation Range  $\Phi$ [mm]: 1,40 - 1,70  
 Seal(s): 15366022

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2083 0,50 / 15366022		1,55	75	1,15	0,05	1,80	0,10	3,10	0,10	2,90	0,10

## Cable type code legend:

2083:

Industry Designator: ISO  
 Conductor Material: COPPER  
 Conductor Plating: NONE  
 Insul. Material: PVC (YW)  
 Insul. Wall Designator: THIN



# Crimp Information Sheet

Terminal Part Number: 15326266  
 Surface Plating: SN  
 Material Thickness [mm]: 0,30  
 Cross Section [mm<sup>2</sup>]: 0,30 | 0,50



*This document is non-contractual  
 and for information only.  
 For more information, please  
 consult your local sales office*

Cable Type codes: 3004  
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY  
 Insulation Range  $\Phi$ [mm]: 1,30 - 1,70  
 Seal(s): 15366022 | 15344324

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
3004 0,30 / 15366022		1,40	59	1,05	0,05	1,75	0,10	3,00	0,10	3,00	0,10
3004 0,30 / 15344324		1,40	59	1,05	0,05	1,75	0,10	2,60	0,10	3,00	0,10
3004 0,50 / 15366022		1,60	80	1,10	0,05	1,80	0,10	2,90	0,10	3,00	0,10

## Cable type code legend:

3004: AVSS  
 Industry Designator: JIS/JA  
 Conductor Material: COPPER  
 Conductor Plating: NONE  
 Insul. Material: PVC, XLPE, X-PVC  
 Insul. Wall Designator: THIN



# Crimp Information Sheet

Terminal Part Number: 15326266  
 Surface Plating: SN  
 Material Thickness [mm]: 0,30  
 Cross Section [mm<sup>2</sup>]: 0,50

*This document is non-contractual  
 and for information only.  
 For more information, please  
 consult your local sales office*



Cable Type codes: 8000  
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY  
 Insulation Range  $\Phi$ [mm]: 1,40 - 1,60  
 Seal(s): 15366022

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
8000 0,50 / 15366022		1,50	75	1,15	0,05	1,70	0,10	2,90	0,10	2,90	0,10

## Cable type code legend:

8000:

Industry Designator: N/G  
 Conductor Material: COPPER  
 Conductor Plating: NONE  
 Insul. Material: SYNTHRESIN  
 Insul. Wall Designator: THIN



# Crimp Information Sheet

Terminal Part Number: 15326266  
 Surface Plating: SN  
 Material Thickness [mm]: 0,30  
 Cross Section [mm<sup>2</sup>]: 0,50

*This document is non-contractual  
 and for information only.  
 For more information, please  
 consult your local sales office*

Cable Type codes: 9000  
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY  
 Insulation Range  $\Phi$ [mm]: 1,90 - 2,05  
 Seal(s): 15305351

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
9000 0,50 / 15305351		1,98	80	1,10	0,05	1,80	0,10	3,10	0,10	3,00	0,10

## Cable type code legend:

9000:

Industry Designator: MISC  
 Conductor Material: COPPER  
 Conductor Plating: NONE  
 Insul. Material: PVDF  
 Insul. Wall Designator: MIX

