



SAFETY DATA SHEET

DOW CHEMICAL COMPANY LIMITED

Safety Data Sheet according to Reg. (EU) No 2015/830

Product name: DOWSIL™ 732 Multi-Purpose Sealant, Black

Revision Date: 29.08.2018

Version: 3.0

Date of last issue: 20.02.2018

Print Date: 30.08.2018

DOW CHEMICAL COMPANY LIMITED encourages and expects you to read and understand the entire (M)SDS, as there is important information throughout the document. We expect you to follow the precautions identified in this document unless your use conditions would necessitate other appropriate methods or actions.

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1 Product identifier

Product name: DOWSIL™ 732 Multi-Purpose Sealant, Black

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses: Adhesive, binding agents

1.3 Details of the supplier of the safety data sheet

COMPANY IDENTIFICATION

DOW CHEMICAL COMPANY LIMITED
STATION ROAD, BIRCH VALE, HIGH PEAK
DERBYSHIRE
England
SK22 1BR
UNITED KINGDOM

Customer Information Number:

+44 (0) 1663 746518

SDSQuestion@dow.com

Fax:

+44 (0) 1663 746605

1.4 EMERGENCY TELEPHONE NUMBER

24-Hour Emergency Contact: 0031 115 694 982

Local Emergency Contact: 00 31 115 69 4982

SECTION 2: HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008:

Not a hazardous substance or mixture according to Regulation (EC) No. 1272/2008.

2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008:

Not a hazardous substance or mixture according to Regulation (EC) No. 1272/2008.

Precautionary statements

P271 Use only outdoors or in a well-ventilated area.

2.3 Other hazards

This product contains dodecamethylcyclhexasiloxane (D6) that has been identified by the Member State Committee of ECHA as fulfilling the vPvB criteria laid down in Annex XIII to Regulation (EC) No 1907/2006. See Section 12 for additional information.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

Chemical nature: Silicone elastomer

3.2 Mixtures

This product is a mixture.

CASRN / EC-No. / Index-No.	REACH Registration Number	Concentration	Component	Classification: REGULATION (EC) No 1272/2008
----------------------------------	---------------------------------	---------------	-----------	--

PBT and vPvB substance

CASRN 540-97-6 EC-No. 208-762-8 Index-No. -	-	>= 0.82 - <= 0.86 %	Dodecamethyl cyclhexasiloxane	Not classified
--	---	---------------------	----------------------------------	----------------

SECTION 4: FIRST AID MEASURES

4.1 Description of first aid measures**General advice:**

If potential for exposure exists refer to Section 8 for specific personal protective equipment.

Inhalation: Move person to fresh air; if effects occur, consult a physician.

Skin contact: Wash off with plenty of water.

Eye contact: Flush eyes thoroughly with water for several minutes. Remove contact lenses after the initial 1-2 minutes and continue flushing for several additional minutes. If effects occur, consult a physician, preferably an ophthalmologist.

Ingestion: No emergency medical treatment necessary.

4.2 Most important symptoms and effects, both acute and delayed:

Aside from the information found under Description of first aid measures (above) and Indication of immediate medical attention and special treatment needed (below), any additional important symptoms and effects are described in Section 11: Toxicology Information.

4.3 Indication of any immediate medical attention and special treatment needed

Notes to physician: No specific antidote. Treatment of exposure should be directed at the control of symptoms and the clinical condition of the patient.

SECTION 5: FIREFIGHTING MEASURES

5.1 Extinguishing media

Suitable extinguishing media: Water spray Alcohol-resistant foam Carbon dioxide (CO₂) Dry chemical

Unsuitable extinguishing media: None known.

5.2 Special hazards arising from the substance or mixture

Hazardous combustion products: Carbon oxides Silicon oxides

Unusual Fire and Explosion Hazards: Exposure to combustion products may be a hazard to health.

5.3 Advice for firefighters

Fire Fighting Procedures: Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. Use water spray to cool unopened containers. Remove undamaged containers from fire area if it is safe to do so. Evacuate area.

Special protective equipment for firefighters: Wear self-contained breathing apparatus for firefighting if necessary. Use personal protective equipment.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures: Follow safe handling advice and personal protective equipment recommendations.

6.2 Environmental precautions: Discharge into the environment must be avoided. Prevent further leakage or spillage if safe to do so. Retain and dispose of contaminated wash water. Local authorities should be advised if significant spillages cannot be contained.

6.3 Methods and materials for containment and cleaning up: Wipe up or scrape up and contain for salvage or disposal. Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable. For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

6.4 Reference to other sections:

See sections: 7, 8, 11, 12 and 13.

SECTION 7: HANDLING AND STORAGE

7.1 Precautions for safe handling: Take care to prevent spills, waste and minimize release to the environment. Handle in accordance with good industrial hygiene and safety practice. Use only with adequate ventilation. See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

7.2 Conditions for safe storage, including any incompatibilities: Keep in properly labelled containers. Store in accordance with the particular national regulations.

Do not store with the following product types: Strong oxidizing agents.
Unsuitable materials for containers: None known.

7.3 Specific end use(s): See the technical data sheet on this product for further information.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 Control parameters

If exposure limits exist, they are listed below. If no exposure limits are displayed, then no values are applicable.

Derived No Effect Level

Dodecamethyl cyclohexasiloxane

Workers

<i>Acute systemic effects</i>		<i>Acute local effects</i>		<i>Long-term systemic effects</i>		<i>Long-term local effects</i>	
Dermal	Inhalation	Dermal	Inhalation	Dermal	Inhalation	Dermal	Inhalation
n.a.	n.a.	n.a.	6.1 mg/m ³	n.a.	11 mg/m ³	n.a.	1.22 mg/m ³

Consumers

<i>Acute systemic effects</i>			<i>Acute local effects</i>		<i>Long-term systemic effects</i>			<i>Long-term local effects</i>	
Dermal	Inhalation	Oral	Dermal	Inhalation	Dermal	Inhalation	Oral	Dermal	Inhalation
n.a.	n.a.	1.7 mg/kg bw/day	n.a.	1.5 mg/m ³	n.a.	2.7 mg/m ³	1.7 mg/kg bw/day	n.a.	0.3 mg/m ³

Predicted No Effect Concentration

Dodecamethyl cyclohexasiloxane

Compartment	PNEC
Fresh water sediment	2.826 mg/kg
Marine sediment	0.282 mg/kg
Soil	3.336 mg/kg
Sewage treatment plant	> 1.0 mg/l

8.2 Exposure controls

Engineering controls: Use local exhaust ventilation, or other engineering controls to maintain airborne levels below exposure limit requirements or guidelines. If there are no applicable exposure

limit requirements or guidelines, general ventilation should be sufficient for most operations. Local exhaust ventilation may be necessary for some operations.

Individual protection measures

Eye/face protection: Use safety glasses (with side shields). Safety glasses (with side shields) should be consistent with EN 166 or equivalent.

Skin protection

Hand protection: Chemical protective gloves should not be needed when handling this material. Consistent with general hygienic practice for any material, skin contact should be minimized.

Other protection: No precautions other than clean body-covering clothing should be needed.

Respiratory protection: Respiratory protection should be worn when there is a potential to exceed the exposure limit requirements or guidelines. If there are no applicable exposure limit requirements or guidelines, wear respiratory protection when adverse effects, such as respiratory irritation or discomfort have been experienced, or where indicated by your risk assessment process. For most conditions, no respiratory protection should be needed; however, if handling at elevated temperatures without sufficient ventilation, use an approved air-purifying respirator.

Use the following CE approved air-purifying respirator: Organic vapor cartridge, type A (boiling point >65 °C, meeting standard EN 14387).

Environmental exposure controls

See SECTION 7: Handling and storage and SECTION 13: Disposal considerations for measures to prevent excessive environmental exposure during use and waste disposal.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

Appearance

Physical state	paste
Color	black
Odor	acetic acid
Odor Threshold	No data available
pH	Not applicable
Melting point/range	No data available
Freezing point	No data available
Boiling point (760 mmHg)	Not applicable
Flash point	Not applicable
Evaporation Rate (Butyl Acetate = 1)	Not applicable
Flammability (solid, gas)	Not classified as a flammability hazard
Lower explosion limit	No data available
Upper explosion limit	No data available
Vapor Pressure	Not applicable
Relative Vapor Density (air = 1)	No data available
Relative Density (water = 1)	1.04

Water solubility	No data available
Partition coefficient: n-octanol/water	No data available
Auto-ignition temperature	No data available
Decomposition temperature	No data available
Dynamic Viscosity	Not applicable
Kinematic Viscosity	Not applicable
Explosive properties	Not explosive
Oxidizing properties	The substance or mixture is not classified as oxidizing.

9.2 Other information

Liquid Density	1.04 g/cm ³
Molecular weight	No data available
Particle size	No data available

NOTE: The physical data presented above are typical values and should not be construed as a specification.

SECTION 10: STABILITY AND REACTIVITY

10.1 Reactivity: Not classified as a reactivity hazard.

10.2 Chemical stability: Stable under normal conditions.

10.3 Possibility of hazardous reactions: Can react with strong oxidizing agents.

10.4 Conditions to avoid: None known.

10.5 Incompatible materials: Oxidizing agents

10.6 Hazardous decomposition products: Formaldehyde.

SECTION 11: TOXICOLOGICAL INFORMATION

Toxicological information appears in this section when such data is available.

11.1 Information on toxicological effects

Acute toxicity

Acute oral toxicity

Very low toxicity if swallowed. Harmful effects not anticipated from swallowing small amounts.

As product: Single dose oral LD50 has not been determined.

Based on information for component(s):
LD50, Rat, > 5,000 mg/kg Estimated.

Acute dermal toxicity

Prolonged skin contact is unlikely to result in absorption of harmful amounts.

As product: The dermal LD50 has not been determined.

Based on information for component(s):
LD50, > 2,000 mg/kg Estimated.

Acute inhalation toxicity

At room temperature, exposure to vapor is minimal due to low volatility; vapor from heated material may cause respiratory irritation.

As product: The LC50 has not been determined.

Skin corrosion/irritation

Prolonged exposure not likely to cause significant skin irritation.

Serious eye damage/eye irritation

May cause slight temporary eye irritation.

Corneal injury is unlikely.

May cause mild eye discomfort.

Sensitization

For skin sensitization:

Contains component(s) which did not cause allergic skin sensitization in guinea pigs.

For respiratory sensitization:

No relevant data found.

Specific Target Organ Systemic Toxicity (Single Exposure)

Evaluation of available data suggests that this material is not an STOT-SE toxicant.

Specific Target Organ Systemic Toxicity (Repeated Exposure)

Based on information for component(s):

Based on available data, repeated exposures are not anticipated to cause significant adverse effects.

Carcinogenicity

Based on information for component(s): Did not cause cancer in long-term animal studies which used routes of exposure considered relevant to industrial handling. Positive results have been reported in other studies using routes of exposure not relevant to industrial handling. Contains an additional component(s) that is/are encapsulated in the product and are not expected to be released under normal processing conditions or foreseeable emergency.

Teratogenicity

Based on information for component(s): Did not cause birth defects or any other fetal effects in laboratory animals.

Reproductive toxicity

Based on information for component(s): In animal studies, did not interfere with reproduction.

Mutagenicity

For this family of materials: In vitro genetic toxicity studies were negative. Animal genetic toxicity studies were negative.

Aspiration Hazard

Based on physical properties, not likely to be an aspiration hazard.

COMPONENTS INFLUENCING TOXICOLOGY:

Dodecamethyl cyclohexasiloxane

Acute inhalation toxicity

The LC50 has not been determined.

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicological information appears in this section when such data is available.

12.1 Toxicity

Dodecamethyl cyclohexasiloxane

Acute toxicity to algae/aquatic plants

Not expected to be acutely toxic to aquatic organisms.

No toxicity at the limit of solubility

ErC50, Pseudokirchneriella subcapitata (green algae), 72 Hour, > 0.002 mg/l

Chronic toxicity to aquatic invertebrates

No toxicity at the limit of solubility

NOEC, Daphnia magna (Water flea), 21 d, 0.0046 mg/l

12.2 Persistence and degradability

Dodecamethyl cyclohexasiloxane

Biodegradability: Based on stringent OECD test guidelines, this material cannot be considered as readily biodegradable; however, these results do not necessarily mean that the material is not biodegradable under environmental conditions.

10-day Window: Fail

Biodegradation: 57 %

Exposure time: 28 d

Method: OECD Test Guideline 301B

12.3 Bioaccumulative potential

Dodecamethyl cyclohexasiloxane

Bioaccumulation: Bioconcentration potential is low (BCF less than 100 or log Pow greater than 7).

Partition coefficient: n-octanol/water(log Pow): 8.87

12.4 Mobility in soil

Dodecamethyl cyclohexasiloxane

Potential for mobility in soil is very high (Koc between 0 and 50).

12.5 Results of PBT and vPvB assessment

Dodecamethyl cyclohexasiloxane

Dodecamethyl cyclohexasiloxane (D6) meets the current REACh Annex XIII criteria for vPvB. However, D6 does not behave similarly to known PBT/vPvB substances. The weight of scientific evidence from field studies shows that D6 is not biomagnifying in aquatic and terrestrial food webs. D6 in air will degrade by reaction with naturally occurring hydroxyl radicals in the atmosphere. Any D6 in air that does not degrade by reaction with hydroxyl radicals is not expected to deposit from the air to water, to land, or to living organisms.

12.6 Other adverse effects

Dodecamethyl cyclohexasiloxane

This substance is not on the Montreal Protocol list of substances that deplete the ozone layer.

SECTION 13: DISPOSAL CONSIDERATIONS

13.1 Waste treatment methods

Do not dump into any sewers, on the ground, or into any body of water. This product, when being disposed of in its unused and uncontaminated state should be treated as a hazardous waste according to EC Directive 2008/98/EC. Any disposal practices must be in compliance with all national and provincial laws and any municipal or local by-laws governing hazardous waste. For used, contaminated and residual materials additional evaluations may be required.

The definitive assignment of this material to the appropriate EWC group and thus its proper EWC code will depend on the use that is made of this material. Contact the authorized waste disposal services.

SECTION 14: TRANSPORT INFORMATION

Classification for ROAD and Rail transport (ADR/RID):

- | | |
|-----------------------------------|---|
| 14.1 UN number | Not applicable |
| 14.2 UN proper shipping name | Not regulated for transport |
| 14.3 Transport hazard class(es) | Not applicable |
| 14.4 Packing group | Not applicable |
| 14.5 Environmental hazards | Not considered environmentally hazardous based on available data. |
| 14.6 Special precautions for user | No data available. |

Classification for SEA transport (IMO-IMDG):

- | | |
|---|---|
| 14.1 UN number | Not applicable |
| 14.2 UN proper shipping name | Not regulated for transport |
| 14.3 Transport hazard class(es) | Not applicable |
| 14.4 Packing group | Not applicable |
| 14.5 Environmental hazards | Not considered as marine pollutant based on available data. |
| 14.6 Special precautions for user | No data available. |
| 14.7 Transport in bulk according to Annex I or II of MARPOL | Consult IMO regulations before transporting ocean bulk |

73/78 and the IBC or IGC Code**Classification for AIR transport (IATA/ICAO):**

- 14.1 UN number Not applicable
- 14.2 UN proper shipping name Not regulated for transport
- 14.3 Transport hazard class(es) Not applicable
- 14.4 Packing group Not applicable
- 14.5 Environmental hazards Not applicable
- 14.6 Special precautions for user No data available.

This information is not intended to convey all specific regulatory or operational requirements/information relating to this product. Transportation classifications may vary by container volume and may be influenced by regional or country variations in regulations. Additional transportation system information can be obtained through an authorized sales or customer service representative. It is the responsibility of the transporting organization to follow all applicable laws, regulations and rules relating to the transportation of the material.

SECTION 15: REGULATORY INFORMATION

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**REACH Regulation (EC) No 1907/2006**

This product contains only components that have been either pre-registered, registered, are exempt from registration, are regarded as registered or are not subject to registration according to Regulation (EC) No. 1907/2006 (REACH). The aforementioned indications of the REACH registration status are provided in good faith and believed to be accurate as of the effective date shown above. However, no warranty, express or implied, is given. It is the buyer's/user's responsibility to ensure that his/her understanding of the regulatory status of this product is correct.

Authorisation status under REACH:

The following substance/s contained in this product might be or is/are subject to authorization in accordance with REACH:

CAS-No.: 540-97-6	Name: Dodecamethyl cyclohexasiloxane
-------------------	--------------------------------------

Authorisation status: listed in the Candidate List of Substances of Very High Concern for Authorisation

Authorisation number: Not available

Sunset date: Not available

Exempted (Categories of) Uses: Not available

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.

Listed in Regulation: Not applicable

15.2 Chemical safety assessment

Not applicable

SECTION 16: OTHER INFORMATION

Classification and procedure used to derive the classification for mixtures according to Regulation (EC) No 1272/2008

This product is not classified as dangerous according to EC criteria.

Revision

Identification Number: 4103039 / A279 / Issue Date: 29.08.2018 / Version: 3.0

Most recent revision(s) are noted by the bold, double bars in left-hand margin throughout this document.

Full text of other abbreviations

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

Information Source and References

This SDS is prepared by Product Regulatory Services and Hazard Communications Groups from information supplied by internal references within our company.

DOW CHEMICAL COMPANY LIMITED urges each customer or recipient of this (M)SDS to study it carefully and consult appropriate expertise, as necessary or appropriate, to become aware of and understand the data contained in this (M)SDS and any hazards associated with the product. The information herein is provided in good faith and believed to be accurate as of the effective date shown above. However, no warranty, express or implied, is given. Regulatory requirements are subject to change and may differ between various locations. It is the buyer's/user's responsibility to ensure that his activities comply with all federal, state, provincial or local laws. The information presented here pertains only to the product as shipped. Since conditions for use of the product are not under the control of the manufacturer, it is the buyer's/user's duty to determine the conditions necessary for the safe use of this product. Due to the proliferation of sources for information such as manufacturer-specific (M)SDSs, we are not and cannot be responsible for (M)SDSs obtained from any source other than ourselves. If you have obtained an (M)SDS from another source or if you are not sure that the (M)SDS you have is current, please contact us for the most current version.

GB