


T495, Tantalum, MnO2 Tantalum, 150 uF, 10%, 4 VDC, SMD, MnO2, Molded, Low ESR, 250 mOhms, 6032, Height Max = 2.8mm



General Information

Supplier:	KEMET
Series:	T495
Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Description:	SMD, MnO2, Molded, Low ESR
Features:	Low ESR
RoHS:	Yes
Termination:	Tin
Shelf Life:	156 Weeks
MSL:	1

Dimensions

Footprint	6032
L	6mm +/-0.3mm
W	3.2mm +/-0.3mm
H	2.5mm +/-0.3mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.2mm +/-0.1mm
A	2.9mm MIN
B	0.5mm +/-0.15mm
E	2.4mm REF
G	2.8mm REF
P	0.9mm REF
R	1mm REF
X	0.1mm +/-0.1mm

Specifications

Capacitance:	150 uF
Capacitance Tolerance:	10%
Voltage DC:	4 VDC (85C), 2.68 VDC (125C)
Temperature Range:	-55/+125C
Rated Temperature:	85C
Dissipation Factor:	8.00% 120Hz 20C
Failure Rate:	N/A
Resistance:	250 mOhms (100kHz)
Ripple Current:	663 mAmps (100kHz 25C), 596.7 mAmps (85C), 265.2 mAmps (125C)
Leakage Current:	6 uA (5min 20C)

Packaging Specifications

Weight:	224.48 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500