



T495, Tantalum, MnO2 Tantalum, 6.8 uF, 20%, 50 VDC, SMD, MnO2, Molded, Low ESR, 300 mOhms, 7343, Height Max = 3.1mm


CATHODE (-) END VIEW



SIDE VIEW




ANODE (+) END VIEW



Termination cutout at KEMET's option, either end.

BOTTOM VIEW



**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	T495
<b>Dielectric:</b>	MnO2 Tantalum
<b>Style:</b>	SMD Chip
<b>Description:</b>	SMD, MnO2, Molded, Low ESR
<b>Features:</b>	Low ESR
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Shelf Life:</b>	156 Weeks
<b>MSL:</b>	1

**Dimensions**

Footprint	7343
<b>L</b>	7.3mm +/-0.3mm
<b>W</b>	4.3mm +/-0.3mm
<b>H</b>	2.8mm +/-0.3mm
<b>T</b>	0.13mm REF
<b>S</b>	1.3mm +/-0.3mm
<b>F</b>	2.4mm +/-0.1mm
<b>A</b>	3.6mm MIN
<b>B</b>	0.5mm +/-0.15mm
<b>E</b>	3.5mm REF
<b>G</b>	3.5mm REF
<b>P</b>	0.9mm REF
<b>R</b>	1mm REF
<b>X</b>	0.1mm +/-0.1mm

**Specifications**

<b>Capacitance:</b>	6.8 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	50 VDC (85C), 33.5 VDC (125C)
<b>Temperature Range:</b>	-55/+125C
<b>Rated Temperature:</b>	85C
<b>Dissipation Factor:</b>	6.00% 120Hz 20C
<b>Failure Rate:</b>	N/A
<b>Resistance:</b>	300 mOhms (100kHz)
<b>Ripple Current:</b>	707 mAmps (100kHz 25C), 636.3 mAmps (85C), 282.8 mAmps (125C)
<b>Leakage Current:</b>	3.4 uA (5min 20C)

**Packaging Specifications**

<b>Weight:</b>	446.84 mg
<b>Packaging:</b>	T&R, 178mm
<b>Packaging Quantity:</b>	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.