Silicone Grease



RoHS Compliant

Description

The MC002971 Silicone Grease is a translucent, water repelling (hydrophobic), non-melting, and lubricating dielectric grease that provides superior corrosion and arcing resistance for connectors. It is widely applicable because it is safe for most metals, rubbers, plastics, and elastomers. As well, it is usable in many environments due to its high resistance and stability with respect to extreme cold, heat, humidity, and other extreme exposure conditions like high voltages. Voltage arcing can be prevented due to its excellent dielectric properties. Further, because it repels water, it provides excellent oxidation resistance for contacts and relays.

Benefits and Features

- · Stable over wide temperature range and conditions Non-melting
- · Excellent electrical insulator High dielectric strength
- Usable for incidental food contact (Conforms to 21 CFR section 178.3570)
- · Odourless and non-toxic
- Corrosion inhibitor
- · Suitable for Use in Food Facilities as a Non-Food Chemical

Usage Parameters

Properties	Value
Shelf Life a)	5 Year

a) Reported shelf life assumes room temperature storage and unopened container.

Temperature Ranges

Properties	Value	
Constant Service Temperature	-50 to 250°C	
Constant Service Temperature	(-58 to 482°F)	
Character Terranducture of Harming of Double h	0 to 25°C	
Storage Temperature of Unmixed Parts b)	(32 to 77°F)	

b) Cold storage avoids material separation and settling. If storing at 25 °C, mix thoroughly to disperse filler before use.

Principal Components

- Dimethylpolysioxane
- · Amorphous silica

Properties

Electrical Properties	Method	Value	
Volume Resistivity (ρν)	ASTM D 257	$1 \times 10^{13} \Omega$ * cm	
Volume Conductivity (σν)	ASTM D 257	1 × 10 ⁻¹³ S * cm	
Dielectric Strength @ 0.01"	ASTM D 149	500 V/mil (19.7kV/mm)	
Arc Resistance		120 s	
Thermal Properties	Method	Value	
Thermal Conductivity		0.16 W/(m*K)	





Silicone Grease



Grease Properties	Method Value	
Evaporation Loss, 22 h @165 °C (329 °F)	ASTM D 2595	1.40%
Oil Separation, 30 h @165 °C (329 °F)	ASTM D 6184	0.40%
Dropping Point	ASTM D 2265	>304 °C (>579 °F)
Water Washout @38 °C (100 °F) a)	ASTM D 1264	3.2%
Worked Penetration		320
Emcor Rust Test, distilled water	IP 220	#4 b)

a) Bearing dried at 77°C (171°F)

b) Corroded areas covering >5% and <10% of the running track surface

Physical Properties	Method	Value	
Colour	Visual	Translucent	
Odour		None	
Density @25°C (77°F)	ASTM D 1475	1.007 g/mL	
Viscosity	Brookfield	Thixotropic paste	
Lubricant		Yes	
Bleed Resistant		No	
Corrosion Resistant		Yes	
Base Material		Silicone Oil	
Filler		Silica	

Compatibility

Chemical - It is compatible with a wide variety of metal, rubber, and plastic substances such as ignition switches, valve seats, O-rings, sealing rings, transformer connectors, and cables systems.

Storage

Store between 0 and 10°C (32 and 50°F) in dry area to minimize settling. You many also store this product at higher temperatures but this can cause settling. If settling occurs, mix thoroughly until the product is homogeneous again.

Application Instructions

The performance of the MC002971 Silicone Grease depends on surface preparation. Improperly prepared contact surfaces can degrade the oxidation protection, dielectric properties, and lubrication characteristics by trapping contaminants between the surface and the grease. The thickness and coverage should be adjusted to meet your needs.

Prerequisites

- Clean and dry the surface of the substrate to remove other oils and greases, as well as dust, water, solvents, or any other contaminants.
- · (Optional) Wear gloves to avoid contaminating the surface and to avoid possible skin irritation.

Equipment

- · Lint free cloth (for cleaning contact and for wiping excess residue)
- Spatula or stick application tools (sized appropriately for your application)
- Isopropyl alcohol or other residue-free organic solvents (for cleaning)

NOTE: Thoroughly clean oil-based cleaners that are designed to leave a film on the metal surface.





Silicone Grease



To apply the paste

- 1. Wipe the contact with a lint-free cloth.
- 2. Clean the contacts with isopropyl alcohol or other non-oil based cleaner.
- 3. Once dry, apply the paste with the application tool to the contact, ensuring adequate coverage and desired thickness.

Packaging

Packaging	Net Volume		Net W	/eight
Tube	85 mL	2.87 fl oz	85.6 g	3.02 oz

Part Number Table

Description	Part Number
Silicone Grease, Translucent, 85mL, Tube	MC002971

Important Notice: This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com www.farnell.com www.newark.com

