

3GAA102530-ASJ



M3AA 100LC 4



General Information

Product ID	3GAA102530-ASJ
ABB Type Designation	M3AA 100LC 4
Catalog Description	M3AA 100LC 4

Additional Information

ABB Type Designation	M3AA 100LC 4
Bearing	6306-2Z/C3
Bearing NDE	6205-2Z/C3
Country of Origin	Poland (PL) Finland (FI) Romania (RO)

Customs Tariff Number	85015220
-----------------------	----------

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	2.20 kW	1455 r/min	4.60 A	0.800	86.70 %	14.40 N·m	7.90
D	--	50 Hz	230 V	2.20 kW	1455 r/min	8.00 A	0.800	86.70 %	14.40 N·m	7.90
Y	--	50 Hz	415 V	2.20 kW	1458 r/min	4.50 A	0.800	86.70 %	14.30 N·m	8.30

Gross Weight	30 kg
--------------	-------

IC Class	IC411
----------	-------

IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 86.7 % Partial Load (75%) 86.3 % Partial Load (50%) 84.0 %
-----------------------	---

IM Class	IMB3 IM1001
----------	-------------

IP Class	IP55
----------	------

Insulation Class	ICLF
------------------	------

Invoice Description	M3AA 100LC 4
---------------------	--------------

Made To Order	No
---------------	----

Minimum Order Quantity	1 piece
------------------------	---------

Order Multiple	1 piece
----------------	---------

Package Level 1 Units	0 carton
-----------------------	----------

Poles (High)	4
--------------	---

Product Name	3-Phase squirrel cage motor
--------------	-----------------------------

Product Net Weight	25 kg
--------------------	-------

Product Type	3AA0_M3AA_AA
--------------	--------------

Quote Only	No
------------	----

Replaced Product ID (OLD)	3GAA102613-ASJ
Selling Unit of Measure	piece
Stocked At (Warehouses)	Central Stock Europe Central Stock Nordic Central Stock Spain CSI
Temperature Class Default	--
Two Speed Motor	No
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

