

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2016495000](#)
Status: **Active**
Overview: [Spot-On Wire-to-Board Connector System](#)
Description: [Spot-On Crimp Terminal, Female, Matte Tin \(Sn\) Plating, 24-28 AWG](#)

Documents:

Drawing (PDF)	Application Specification 2016440000-A01 (PDF)
Product Specification 2016440000-000 (PDF)	Packaging Specification 2016499200-200 (PDF)
Product Specification 2016470000-000 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 2016440000-A00 (PDF)	

General

Product Family	Crimp Terminals
Series	201649
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	Spot-On Wire-to-Board Connector System
Product Name	Spot-On
UPC	889056814546

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Net Weight	42.000/mg
Packaging Type	Reel
Plating min - Mating	1.000µm
Plating min - Termination	1.000µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.80-1.15mm
Wire Size AWG	24, 26, 28
Wire Size mm ²	0.113-0.283


Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	100V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification	2016440000-A00, 2016440000-A01
Crimp Specification	2016490000-C00
Packaging Specification	2016499200-200
Product Specification	2016440000-000, 2016470000-000
Sales Drawing	2016490000-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[201649](#) Series

Use With

Spot-On Receptacle Housing [201644](#) ,
[201647](#)