

RoHS
Compliant



Application

A multipair high performance cable that consists of twisted pair conductors, used mainly for data transmission. Category 5E is recommended for all new installations, supports a frequency range of up to 100MHz and is designed for transmission speeds of up to 1 gigabit per second (Gigabit Ethernet).

Characteristics

Temperature Rating	: -20°C to +50°C
Minimum Bending Radius	: 8 × overall diameter
Core Identification	: Pair 1: Blue, White/Blue Pair 2: Orange, White/Orange Pair 3: Green, White/Green Pair 4: Brown, White/Brown
Sheath Colour	: Black

Cable Standards

ISO/IEC 11801, TIA 568C.2

Construction

Conductor

Class 1 solid copper conductor

Insulation

HDPE (High Density Polyethylene)

Sheath

PE (Polyethylene)

This product range is available on reels of 305m or per metre

Dimensions

No. of Pairs (24 AWG)	Nominal Diameter Over Insulation mm	Nominal Overall Diameter mm	Nominal Weight kg/305m box
4	0.86	5.1	10

Performance Characteristics

Frequency MHz	Attenuation dB/100m	NEXT dB	PS-NEXT dB	RL dB	ELFEXT dB	PS-ELFEXT dB/100m	Phase Delay ns
1	2	65.3	62.3	20	63.8	60.8	570
4	4.1	56.3	53.3	23	51.8	48.8	552

Unscreened Cat 5e, U/UTP Cable



Frequency MHz	Attenuation dB/100m	NEXT dB	PS-NEXT dB	RL dB	ELFEXT dB	PS-ELFEXT dB/100m	Phase Delay ns
8	5.8	51.8	48.8	24.5	45.7	42.7	546.73
10	6.5	50.3	47.3	25	43.8	40.8	545.38
16	8.2	47.2	44.4	25	39.7	36.7	543
20	9.3	45.8	42.8	25	37.8	34.8	542.05
25	10.4	44.3	41.3	24.3	35.8	32.8	541.2
31.25	11.7	42.9	39.9	23.6	33.9	30.9	540.44
62.5	17	38.4	35.4	21.5	27.9	24.9	538.55
100	22	35.3	32.3	20.1	23.8	20.8	537.6

Electrical Characteristics

Impedance (1-100MHz) Ω	Maximum DC Resistance of Conductor at 20°C Ω/km	Maximum Resistance Unbalance % max
100±15	115	5

Part Number Table

Description	Cable Length	Part Number
Unscreened Network Cable, Cat 5e, U/UTP, PE, 4 Pair, 24AWG, Black	305m or per metre	PP002136

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell Limited 2016.