


PRODUCT DATASHEET

HB 95 W 6500 K 90DEG IP65 BK

HIGH BAY Gen 2 | High-bay luminaires up to 135 lm/W



AREAS OF APPLICATION

- Replacement for high bay luminaires with mercury vapor or metal halide lamps
- Warehouses
- Logistics halls
- Industry
- Indoor and outdoor
- High ceiling (e.g. in shopping malls, airports, commercial buildings, lobbies)

PRODUCT BENEFITS

- High luminous efficacy
- Exclusive LEDVANCE design
- Energy savings of up to 60 % compared to conventional high bay luminaires
- 5 years guarantee
- Optimized weight and size due to compact design

PRODUCT FEATURES

- Luminous efficacy: up to 135 lm/W
- Type of protection: IP65
- Available with beam angle: 70°, 90°, 110°



TECHNICAL DATA

Electrical data

Nominal wattage	95.00 W
Operating mode	Electronic control gear (ECG)
Nominal voltage	100...240 V
Power factor λ	≥ 0.95
Mains frequency	50/60 Hz


Photometrical data

Color temperature	6500 K
Luminous efficacy	135 lm/W
Luminous flux	13000 lm
Standard deviation of color matching	≤ 5 sdc _m
Light color (designation)	Cool Daylight
Color rendering index Ra	>80

Light technical data

Beam angle	90.00 °
------------	---------

Dimensions & weight



Diameter	285.0 mm
Height	129.5 mm
Product weight	3135.00 g
Cable length	1500 mm

Colors & materials

Body material	Aluminum
Housing color	Black
Product color	Black

Temperatures & operating conditions

Ambient temperature range	-30...50 °C
----------------------------------	-------------

Lifespan

Lifespan L70 at 25 °C	50000 h
Lifespan L80 at 25 °C	35000 h
Lifespan L90 at 25 °C	20000 h
Number of switching cycles	50000

Additional product data

Mounting type	Suspended/Surface
Mounting location	Ceiling



Capabilities

Dimmable	No
Type of connection	Cable, 3-pole
LED module replaceable	Not replaceable

Certificates & standards

Protection class IK (shock resistance)	IK08
Glow Wire Test according to IEC 695-2-1	650 °C
Photobiological safety group	RG 0
Protection class	I
Type of protection	IP65
Standards	CE/CB/TÜV SÜD/RoHS

Light Distribution



LDC typ cone

LDC typ polar

EQUIPMENT / ACCESSORIES

- Mounting hook and brackets included

LOGISTICAL DATA

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075074347	HB 95 W 6500 K 90DEG IP65 BK	Shipping carton box 1	334 mm x 334 mm x 188 mm	20.97 dm ³	3605.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see
 ▶ www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.