

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	0010112173
Status:	Active
Overview:	KK® Interconnect System - Molex
Description:	KK 254 Crimp Housing, High Pressure, 17 Circuits, Natural

Documents:

[3D Model](#)
[Packaging Specification PK-7880-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-7879-001 \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	<u>7880</u>
Application	Signal, Wire-to-Board
Overview	<u>KK® Interconnect System - Molex</u>
Product Name	KK 254
UPC	800753824447

Physical

Circuits (maximum)	17
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	1.666/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Stackable	No
Temperature Range - Operating	See Product Specification

Solder Process Data


Lead-free	Process Capability	N/A
-----------	--------------------	-----

Material Info

Engineering Number 7880-17B

Reference - Drawing Numbers

Packaging Specification	PK-7880-001-001
Product Specification	PS-7879-001
Sales Drawing	SD-7880



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

7880 Series

Mates With

KK254 PCB Headers 42375 , 42377 , 42376
, 4030 , 6373 , 6410

Use With

7879 KK High Pressure Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION