

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1718560003

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

2.54mm Pitch, KK 254 RPC Vertical Header with Friction Lock, Tin (Sn) Plating, Pin Length 12.95mm, Bag, 3 Circuits

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-171856-0001-001 \(PDF\)](#)
- [Product Specification PS-171856-0002-001 \(PDF\)](#)
- [Product Specification TS-171856-0001-001 \(PDF\)](#)
- [Packaging Specification PK-6373-001-000 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

171856

Application

Board-to-Board, Power, Signal, Wire-to-Board

Comments

See Product Specification for maximum current rating by AWG.

See Product Specification for operating temperature range by material.

Overview

KK® Interconnect System - Molex

Product Name

KK 254

UPC

887191376196

Physical

Breakaway

No

Circuits (Loaded)

3

Circuits (maximum)

3

Color - Resin

Black

Durability (mating cycles max)

25

First Mate / Last Break

No

Flammability

94V-1

Glow-Wire Capable

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Metal

Brass

Material - Plating Mating

Matte Tin

Material - Plating Termination

Matte Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

0.332/g

Number of Rows

1

Orientation

Vertical

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

2.54mm

Plating min - Mating

1.524µm

Plating min - Termination

1.524µm

Polarized to Mating Part

Yes

Shrouded

Partial

Stackable

No

Surface Mount Compatible (SMC)

Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

171856 Series

Mates With

4455 , 2695 , 6471

Temperature Range - Operating	-40° to +105°C, -40° to +80°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	500V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	030
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-6373-001-000
Product Specification	PS-171856-0001-001, PS-171856-0002-001, TS-171856-0001-001
Sales Drawing	SD-171856-0001-000, SD-171856-0001-002

This document was generated on 10/22/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION