

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0002062101](#)
Status: **Active**
Overview: Standard .062" Pin and Socket Power Connectors
Description: 1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-02-06-001 \(PDF\)](#)

General

| | |
|-------------------------|--|
| Product Family | Crimp Terminals |
| Series | 1560 |
| Application | Power, Wire-to-Wire |
| Crimp Quality Equipment | Yes |
| Overview | Standard .062" Pin and Socket Power Connectors |
| Packaging Alternative | 02-06-2103 (Loose) |
| Product Name | Standard .062" |
| UPC | 800753616080 |

Physical

| | |
|--------------------------------|----------------------|
| Gender | Male |
| Material - Metal | Brass |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 0.120/g |
| Packaging Type | Reel |
| Plating min - Mating | 0.508µm |
| Plating min - Termination | 0.508µm |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.52-3.05mm |
| Wire Size AWG | 18, 20, 22, 24 |
| Wire Size mm ² | N/A |

Solder Process Data


| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

| | |
|--------------------|-------------|
| Engineering Number | 1560-(P901) |
|--------------------|-------------|

Reference - Drawing Numbers

| | |
|-----------------------|--------------|
| Product Specification | PS-02-06-001 |
| Sales Drawing | SD-1560-* |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[1560 Series](#)