

Industrial Ethernet IE-SW-BL08-8TX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Weidmüller's BasicLine consists of unmanaged Plug & Play switches in a robust IP 30 protected aluminium housing. The equipment can be delivered with Fast Ethernet and Gigabit Ethernet ports and offers an economical solution for industrial Ethernet networks. One variety is fitted with Fast Ethernet and Power-over-Ethernet ports. All the equipment has been developed for use in harsh industrial environments and has international approvals such as CE, cULus, Class I Div. 2 / ATEX and DNV / GL, and is therefore able to be used in many international applications.

- Plug & Play switches in a rugged aluminium housing (IP 30)
- Compact design
- Switches for an economical entry solution
- Fast Ethernet versions with 5 and 8 ports
- Models with copper or fibre-optic interface (multimode and singlemode)
- Full Gigabit Plug and Play switch with 5 ports
- Power-over-Ethernet (PoE) switch with 6 Fast Ethernet ports, 4 of them PoE+ ports
- Approvals: CE, FCC, cULus, Class I Div. 2 / ATEX, DNV / GL

General ordering data

Type	IE-SW-BL08-8TX
Order No.	1240900000
Version	Network switch, unmanaged, Fast Ethernet, Number of ports: 8x RJ45, IP30, -10 °C...60 °C
GTIN (EAN)	4050118028911
Qty.	1 pc(s).

**Industrial Ethernet
IE-SW-BL08-8TX**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Width	50 mm	Width (inches)	1.969 inch
Height	115 mm	Height (inches)	4.528 inch
Depth	70 mm	Depth (inches)	2.756 inch
Weight	275 g	Net weight	275 g

EMC conformity and approvals

EMC standards	FCC Part 15, CISPR (EN55022) Class A, EN 61000-4-2 (ESD), Stage 3, EN 61000-4-3 (RS), Stage 3, EN 61000-4-4 (EFT), Stage 3, EN 61000-4-5 (surge voltage), Stage 3, EN 61000-4-6 (CS), Stage 3, EN 61000-4-8, EN 61000-4-11	Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA IIC T4 Gc
Free fall	according to IEC 60068-2-32	Security	UL508
Ship use	DNV, GL	Shock	according to IEC 60068-2-27
Vibration	according to IEC 60068-2-6		

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	60 °C
Operating temperature, min.	-10 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Guarantee

Time interval	5 years
---------------	---------

Interfaces

DIP switch	1x for enabling/disabling the broadcast storm protection	LED indicator	PWR1, PWR2, 10/100M (TP-Port)
Number of ports	8x RJ45	RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port

MTBF

MTBF	2,428,212 hrs	MTBF	Telcordia (Bellcore), GB
------	---------------	------	--------------------------

Power supply

Connection type	1 removable 4-pin terminal block	Current consumption	0.13 A at 24 V
Overload current protection	1.1 A	Reverse polarity protection	Available
Supply voltage	12/24/48 V DC, 18 to 30 V AC, 47 to 63 Hz, 2 redundant inputs	Supply voltage, max	60 V DC
Supply voltage, min.	9.6 V DC		

Creation date July 2, 2018 11:03:15 AM CEST

**Industrial Ethernet
IE-SW-BL08-8TX**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Switch characteristics**

MAC table size	1 K	Packet buffer size	512 Kbit
----------------	-----	--------------------	----------

Technical data

Housing main material	Aluminium	Protection degree	IP30
Type of mounting	Mounting rail		

Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X), IEEE 802.3x for flow control		

Classifications

ETIM 4.0	EC002598	ETIM 5.0	EC002598
ETIM 6.0	EC000734	eClass 6.2	19-17-01-06
eClass 7.1	19-17-01-06	eClass 8.1	19-17-01-06
eClass 9.0	19-17-01-06	eClass 9.1	19-17-01-06

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	DE_PN4800_160418_001.pdf
Engineering Data	EPLAN, WSCAD, Zuken E3.S
User Documentation	Hardware Installation Guide