







Measuring leads

MLS WG 50/2,5



Product	MLS WG 50/2,5
description	Safety measuring lead, at either end 4 mm diameter safety connector with straight/rectangular outlet and integrated kink protection. Nickel-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, shatter-proof grip sleeve and lead. Color indicator for the recognition of damage to the insulation. In accordance to IEC 61010 standard.
operating instruction	BA453
article-no. / *colour	9340811xx <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;"> 00 black</div> <div style="text-align: center;"> 01 red</div> <div style="text-align: center;"> 02 blue</div> <div style="text-align: center;"> 03 yellow</div> <div style="text-align: center;"> 04 green</div> <div style="text-align: center;"> 88 yellow green</div> </div> <div style="text-align: right; margin-top: 5px;">Ni</div>
technical data	
rated voltage ⁽¹⁾	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT III
rated current ⁽¹⁾ (consider derating curve)	32 A
material plug	brass, nickel plated
housing material	PA
temperature range acc. To IEC61010 ⁽²⁾	-15 °C to +70 °C
inflammability class acc. to UL 94 (only valid for basic material of housing)	V-2
cable length	50 cm
conductor size	2,5 mm ²
cable material	PVC
contact resistance	8 mOhm
standard	IEC 61010

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges

stand: 23.07.2018