





## Measuring leads

### PL 2600 S



Product	PL 2600 S
description	Safety test lead with dual function safety test probe. Tip for penetration of oxide layers and 4 mm diameter pin for insertion into sockets. 4 mm diameter safety connector with straight outlet.
operating instruction	BA452
article-no. / *colour	9341591xx <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  00 black         </div> <div style="text-align: center;">  01 red         </div> <div style="text-align: center;">  02 blue         </div> </div> <div style="text-align: right; margin-top: 10px;"><b>Ni</b></div>
drawing	
<b>technical data</b>	
rated voltage <sup>(1)</sup>	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT II
rated current <sup>(1)</sup> (consider derating curve)	16 A
material plug	brass, nickel plated
housing material	PA, PP
temperature range acc. To IEC61010 <sup>(2)</sup>	-15 °C to +70 °C
inflammability class acc. to UL 94 (only valid for basic material of housing)	HB
cable length	100 cm
conductor size	1 mm <sup>2</sup>
cable material	PVC

4 mm safety system

contact resistance	20 mOhm
standard	IEC 61010

<sup>(1)</sup> for normal environmental conditions -5°C to +40°C

<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges  
stand: 23.07.2018