

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0366640001](#)  
**Status:** **Active**  
**Overview:** [MLX Power Connectors](#)  
**Description:** MLX Crimp Terminal 42024, 10-12 AWG, Reel, Tin (Sn)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-36663-001-001 \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">36664</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current – Maximum per contact 20A if used with <a href="#">36663</a> and <a href="#">36664</a> terminal
Crimp Quality Equipment Overview	Yes
Packaging Alternative	<a href="#">MLX Power Connectors</a>
Product Name	<a href="#">36664-0002 (Loose)</a>
UPC	MLX 822348359370

**Physical**

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.405/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	5.08mm max.
Wire Size AWG	10, 12
Wire Size mm <sup>2</sup>	3.30, 5.25

**Electrical**

Current - Maximum per Contact	20.0A
-------------------------------	-------

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-36663-001-001
Sales Drawing	SD-36664-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[36664 Series](#)

**Use With**

[42021](#) Plug, [42022](#) Receptacle. MLX Double Crimp Terminal [36663](#) , MLX Crimp Terminal [36664](#)