






		Conditions	
<b>cell type:</b>	NiMH		
<b>cell size:</b>	AA		
<b>nominal voltage:</b>	1.2 V		
<b>max. charge voltage:</b>	1.5 V	at standard charge (0.1C / 20°C)	
<b>capacity</b>			
nominal:	2850 mAh	discharge at 0.2C	
minimum:	2650 mAh	discharge at 0.2C	
	2450 mAh	discharge at 1C	
		1.0V end discharge voltage	
		ta: 20°C	
<b>max. continuous discharge current:</b>	5000 mA	ta: 0...45°C	
<b>charge</b>		current	time
standard charge:	285 mA		14....16hrs
quick charge:	800 mA		4hrs
fast charge:	2850 mA		1hr
recommended charge termination control parameters:	0...5 mV 0.8...1 °C 45...50 °C	- ΔV (-deltaV) temperature rise per minute TCO (temperature cut off)	
trickle charge current:	20...80 mA	(recommended)	
continuous overcharge: (less than 1 year)	≤ 200 mA	no conspicuous deformation no leakage	
<b>internal resistance:</b> (impedance)	≤ 30 mΩ	at 1KHz battery fully charged	
<b>life expectancy:</b>	≥ 500 cycles	acc. IEC standard	
<b>self discharge</b>			
charge retention:	≥ 60 %	after 28 days storage at 20°C	
<b>initial capacity:</b>	≥ 900 mAh	within 30 days after delivery discharge at 0.2C	
<b>ambient temperature range:</b>	0...45 °C 10...40 °C - 20...65 °C - 20...50 °C - 20...40 °C - 20...30 °C	standard charge fast charge discharge storage (≤1month) storage (≤3months) storage (≤12months)	
QCT1:	20/2500/35		
QCT2:	30/2350/40		

### Diagrams



### mechanical specifications

cell dimensions			
diameter d1:		14.5 - 0.7	mm
diameter d2:	max.	5.5	mm
height h1:		50.5 - 0.5	mm
height h2:	min.	1.2	mm
weight:		31 ± 2	g
blister card dimensions:		123 x 85	mm
blister card weight (incl. batteries):		132	g



35

	<b>ANSMANN Specifications for model:</b>	<b>AA - 2850mAh</b>
		<b>4pcs blister package</b>
	data sheet no. / part no.	5035212
	supplier no.	701372
	author / date	TG / 13.06.2018

Manufacturer reserves the right to alter or amend the design, model and specification without prior notice