



DIB-100

Order No.: 24.1140

Price upon request

PRODUCTINFOS

DI Boxes

For an optimum signal transmission from musical instruments to a mixer or amplifier. By using a transformer coupling, interferences due to matching problems, e.g. hum loops, are prevented to a large extent. Input and output are galvanically isolated.

For adapting line levels, please use units of the LTR series!

DI box

- 3-fold attenuation switch (0/-20/-40 dB)
- Ground lift switch
- Instrument feed-through output
- Wideband balancing transformer
- Robust metal housing

PRODUCTION PARTNER 04/2013

"The measured values and workmanship give no reason for criticism. When considering the price, too, you can't go wrong."

TECHNICAL SPECIFICATIONS

DIB-100

Type	DI box
Frequency range	15-30,000 Hz, ± 0 dB
Input impedance	50 k Ω
Output impedance	600 Ω (bal.), 50 k Ω (unbal.)
Gain	0/-20/-40 dB
Transmission ratio	10:1
Admiss. ambient temp.	0-40 °C
Dimensions	74 x 45 x 130 mm
Weight	560 g
Inputs	6.3 mm jack, unbal
Outputs	6.3 mm jack, unbal., par. out XLR, bal.

DIB-100

Width	74 mm
Height	45 mm
Depth	130 mm
Weight	