

**battery type:** lithium primary battery  
**battery size:** CR-2 (CR15H270)  
**chemical system:** Manganese Dioxide Lithium Battery

**nominal voltage:** 3.0 V  
**open circuit voltage:** 3.0...3.5 V  
**closed circuit voltage:** 2.9...3.4 V

**conditions, remarks**  
 new battery  
 measured after 1s under load of 50Ω

**capacity** measurements at 23°C ambient; new battery

**rated:** 850 mAh discharge at 1mA constant current; 24hours/day  
 End Voltage (EV): 2.0V




**minimum:** 750 mAh discharge at 10mA constant current; continuous  
 End Voltage (EV): 2.0V

550 mAh discharge at 500mA constant current; continuous  
 End Voltage (EV): 2.0V

**duration** new battery

**pulse load:** load: 900mA for 3s, rest time 27s  
 >900 cycles at 23°C; End Voltage (EV): 1.55V

**discharge diagrams**



**max. discharge current**  
 continuous: 800 mA  
 pulse: 1600 mA

**internal resistance:** ≤ 0.7 Ω sine wave AC method (1kHz; 0.1mA) according to IEC 896-2


**shelf life:** 10 years under proper storage conditions

**ambient temperature range:**  
 - 40...60 °C operating temperature  
 - 20...45 °C storage temperature  
 5...20 °C recommended storage temperature

**relative humidity:** ≤ 75% during storage

**mechanical specifications**

**cell dimensions**  
 diameter Ø1: 15.6 - 0.7 mm  
 diameter Ø2: 6.5 - 1.0 mm  
 height H1: 27.0 - 1.0 mm  
 height H2: 1.5 - 0.9 mm  
 weight: 11 ± 2 g



**blister card dimensions:** 123 x 86 mm  
**weight (incl. battery):** 17 g

	<b>ANSMANN Specifications for model:</b>	<b>CR-2 Lithium Battery</b> <b>1pcs blister package</b>
	data sheet no. / part no.	5020022
	supplier no.	701801
	author / date	TG / 19.01.2018