



DO NOT SCALE DRAWING



REVISION

A INITIAL DRAWING 24.9.15

Part Number	ØA	B Max	C Max	D Length	E Max
B2 0.375 RSBPMC N100	2BA	0.319	0.130	0.375 (3/8")	0.052
B4 0.250 RSBPMC N100	4BA	0.252	0.101	0.250 (1/4")	0.040
B4 0.375 RSBPMC N100				0.375 (3/8")	
B4 0.500 RSBPMC N100				0.500 (1/2")	
B4 0.750 RSBPMC N100				0.750 (3/4")	

NOTES:



DESIGN RIGHT. TR FASTENINGS LTD, 2003
 UNDER NO CIRCUMSTANCES MUST THIS
 DRAWING BE COPIED OR DISCLOSED
 WITHOUT FIRST OBTAINING WRITTEN
 AUTHORITY.

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN Inches
 SURFACE FINISH:
 TOLERANCES: BS 57

	NAME	DATE
DRAWN	Darryl Wilson	24.09.15
CHK'D		
APPVD		

MATERIAL:
 Brass

HEAT TREATMENT:

TITLE:
 Slotted Round Head Machine Screw BS57
 BA Sizes

CUSTOMER PART NUMBER:
 N/A

FINISH:
 BN1 - Commercial Bright Nickel Trivalent

DRAWING NUMBER:
 TR32RSBPMCBA

A4

PROJECTION

