




Suppliers of Quality Assured Cables

Flexible Wiring Cable - CSP Test Leads



Product Type:
Flexible Cable

Application:
Flexible leads used mainly as a flexible connection to or from test equipment.

Standards / Conformances:
REACH and RoHS Compliant

Construction:

Conductor:	Tinned annealed copper to EN60228 Class 6
Insulation:	CSP (Chlorosulphonated Polyethylene) Red, Black

Electrical Characteristics:
Max Voltage 2000V

Physical Characteristics:
Maximum temperature 85°C
Flame propagation IEC 60332-1-2

Part Number	Colour	Length	Conductor Strand	Nom cable diameter /mm	Max. Conductor DC Resistance at 20°C (Ω/Km)
6009342	Black	25m	55/0.15mm	4.0	20.0
6009343	Red	25m	55/0.15mm	4.0	20.0