

# USB-C Multiport Adapter with HDMI - SD Reader - 2x A 1xC - PD 3.0

Product ID: DKT30CSDHPD3



This USB-C multiport adapter with HDMI® turns your MacBook Pro, Dell XPS, or other USB-C™ laptop into a workstation, anywhere you go. The USB Type-C multiport adapter provides 4K HDMI video output, a USB Type-C™ port (data/power), two USB 3.0 Type-A ports, a Gigabit Ethernet port and an SD card reader slot, all through one connection to your laptop's USB-C or Thunderbolt 3™ port. Plus, it offers advanced charging through USB Power Delivery 3.0.

## Enhance Productivity

The portable docking station connects your laptop to a 4K HDMI monitor (4096 x 2160p) to create a powerful workstation. It can also connect to an ultrawide monitor.

## Connect Your Devices

The USB-C to USB 3.0 hub gives you one USB-C port and two USB-A ports to connect your latest and legacy USB devices.

### **Built-In SD Card Reader**

Access your multimedia content with ease. The multiport adapter provides direct access to your SD, SDHC™ and SDXC™ memory cards or microSD cards (with adapter, sold separately).

### **Charge Your Laptop and Peripherals**

With support for USB PD 3.0 (up to 60W), the USB Type-C multiport adapter lets you power and charge your laptop, and power your peripherals when connected to a USB-C power adapter. PD 3.0 features Fast Role Swap to prevent USB data disruption when you switch power sources (USB-C power adapter to bus power).

### **Reliable Network Connectivity**

The Gigabit Ethernet port ensures reliable wired network access.

The DKT30CSDHPD3 is backed by a StarTech.com 3-year warranty and free lifetime technical support.

*Note: To ensure full adapter functionality, your laptop's USB-C port must support USB Power Delivery and DP Alt Mode.*

### Certifications, Reports and Compatibility



### Applications

- Ideal for meetings and making presentations in the boardroom
- Transfer photos, videos or other files from your SD cards to your USB-C laptop, tablet or other device
- Use an HDMI port-equipped television in a hotel room as an external display
- Power the adapter and your laptop through USB-C, using your laptop's power adapter
- Ideal for small workspaces in offices, home offices as well as office hoteling

### Features

- Connect a 4K HDMI monitor to your MacBook Pro or Windows laptop with this USB-C HDMI multiport adapter
- Utilize USB devices when you travel with 3x USB 3.0 ports - 2x USB-A and 1x USB-C
- Power both the multiport adapter and your laptop, using your laptop's USB-C power adapter (supports USB Power Delivery 3.0)
- Get easy access to your SD, SDHC and SDXC memory cards, or microSD cards (with adapter)
- Add wired network connectivity with the Gigabit Ethernet RJ45 port

<b>Hardware</b>	Warranty	3 Years
	4K Support	Yes
	Bus Type	USB-C
	Chipset ID	VIA/VLI - VL102 VIA/VLI - VL817 Genesys Logic - GL823K Parade - PS176 Realtek - RTL8153
	Displays Supported	1
	Fast-Charge Port(s)	No
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0 and 1.1
	<b>Performance</b>	Auto MDIX
Compatible Networks		10/100/1000 Mbps
Full Duplex Support		Yes
Maximum Data Transfer Rate		5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
Maximum Digital Resolutions		4096 x 2160p @ 24Hz or 3840 x 2160p (HDMI) @ 30Hz  UltraWide - 3440 x 1440p @ 60 Hz or 2560x1080 at 60Hz  Lower resolutions are also supported. For example, if the max is 3840 x 2160p (4K), it also supports 2560 x 1600p and 2560 x 1440p.
Memory Media Type		Secure Digital Card  SDHC (Secure Digital High Capacity)  SDXC (Secure Digital eXtended Capacity)  microSD (Micro Secure Digital) (adapter required)  microSDHC (Micro Secure Digital High Capacity) (adapter required)  microSDXC (Micro Secure Digital eXtended Capacity) (adapter required)
Type and Rate		USB 3.0 - 5 Gbit/s
UASP Support		Yes
<b>Connector(s)</b>	Connector Type(s)	1 - USB Type-C (24 pin) USB 3.0 Male  1 - HDMI (19 pin) Female  1 - RJ-45 Female

		<p>2 - USB Type-A (9 pin) USB 3.0 Female</p> <p>1 - SD Slot Female</p> <p>1 - USB Type-C (24 pin) USB 3.0 Female</p>
<b>Software</b>	OS Compatibility	<p>Windows® 7, 8, 8.1, 10</p> <p>Mac OS® 10.11 to 10.13</p> <p>Chrome OS™</p>
<b>Special Notes / Requirements</b>	<b>Note</b>	<p>Not all USB-C ports support the full functionality of the USB Type-C standard. Ensure that your host USB-C port supports USB Power Delivery 2.0 or higher and DP alt mode.</p> <p>The adapter can connect to a host laptop's USB-C port that doesn't support USB Power Delivery 2.0. However, in this configuration if a power adapter is connected to the multifunction adapter, it will not pass power through to your host laptop.</p> <p>A 4K-capable display is required to achieve 3840 x 2160p resolution (4K is also known as 4K x 2K)</p> <p>USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.</p> <p>Your laptop might have specific charging requirements. For example, if your laptop requires exactly 60W of power and an adapter consumes some of the 60W, your laptop might not recognize that it is getting enough power. For more information about Power Delivery, refer to the manufacturer of your hardware.</p>
	System and Cable Requirements	<p>A host laptop with an available USB-C port (to ensure full adapter functionality, the host USB-C port must support USB Power Delivery 2.0 and DP alt mode)</p> <p>Optional: USB-C power adapter (for example, your laptop's USB-C based power adapter)</p>
<b>Power</b>	Power Delivery	60W
	Power Source	USB-Powered
<b>Environmental</b>	Humidity	5~90% RH (Non-condensing)
	Operating Temperature	0°C to 45°C (32°F to 113°F)
	Storage Temperature	-10°C to 85°C (14°F to 185°F)
<b>Physical Characteristics</b>	Cable Length	270 mm [10.6 in]
	Color	Space Gray
	Enclosure Type	Aluminum
	Product Height	15 mm [0.6 in]

	Product Length	270 mm [10.6 in]
	Product Weight	85 g [3 oz]
	Product Width	45 mm [1.8 in]
<b>Packaging Information</b>	Shipping (Package) Weight	0.1 kg [0.3 lb]
<b>What's in the Box</b>	Included in Package	1 - multiport adapter 1 - quick-start guide

Product appearance and specifications are subject to change without notice.