


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5017863092](#)
Status: **Active**
Overview: [FFC-FPC \(SMT\)](#)
Description: 0.50mm Pitch Easy-On FFC-to-Board Connector, Receptacle Housing Assembly, Vertical, Surface Mount, without Grounding Terminals, Separated Gold (Au) Plating, 30 Circuits

Documents:

[3D Model](#) [Packaging Specification SPK-501786-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-501786-004-001 \(PDF\)](#)



General

Product Family	FFC/FPC Connectors
Series	501786
Comments	Requires a custom FFC with notches
Overview	FFC-FPC (SMT)
Product Name	Easy-On
UPC	822350741941

Physical

Actuator Type	FFC-to-Board
Circuits (Loaded)	30
Color - Resin	Black
Contact Position	N/A
Durability (mating cycles max)	20
Mated Height	8.95mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	485.970/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	Yes
PCB Mounting	Surface Mount
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.50mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FFC only

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-501786-001-001
Product Specification	PS-501786-004-001
Sales Drawing	F0500-030-021A, SD-501786-006, SD-501786-007

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[501786 Series](#)

Use With

Plug Jacket [501783-3009](#) . Plug Jacket
Cover [501784-3009](#)
LVDS Cable [15022](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION