

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0528061310

Status:

Active

Overview:

FFC-FPC (Through-Hole)

Description:

1.00mm Pitch Easy-On FFC/FPC Connector, Vertical, Surface Mount Compatible, Non-ZIF, Kinked PC Tails, 13 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-52806-003-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Overview

Product Name

UPC

FFC/FPC Connectors

52806

FFC-FPC (Through-Hole)

Easy-On

800753682832

Physical

Actuator Type

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Contact Position

Durability (mating cycles max)

Flammability

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Mounting

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Wire/Cable Type

Non-ZIF

13

13

Natural

N/A

10

94V-0

5.40mm

Phosphor Bronze

Tin

Tin

High Temperature Thermoplastic

377.201/mg

1

Vertical

3.20mm

No

Through Hole - Kinked Pin

None

1.60mm

Tray

1.00mm

1.00mm

0.914µm

0.914µm

No

No

Yes

-20° to +80°C

FFC/FPC

Electrical


Current - Maximum per Contact

Voltage - Maximum

0.5A

50V AC (RMS)/DC

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/61/2018 (27 June

2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

52806 Series

Reference - Drawing Numbers

Product Specification
Sales Drawing

PS-52806-003-001
SD-52806-**10

This document was generated on 10/08/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION