

# 35 22 115 ESD

## Electronics Pliers ESD



- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- Load-optimised for a more direct feel when working
- For gripping, holding and bending
- Electrically discharging handles - dissipative
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Soft transitions; no sharp edges
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Narrow sleeves pulled up to the head of the pliers enable the tool to be guided securely and comfortably, also between thumb and index finger
- With two-colour dual component grips, black/grey
- Ball bearing chrome steel




### ESD pliers (electrostatic discharge)

electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

<b>Article No.</b>	35 22 115 ESD
<b>EAN</b>	4003773024842
<b>Head</b>	mirror polished
<b>Handles</b>	with multi-component grips
<b>Style</b>	2
<b>B mm</b>	22,5
<b>D mm</b>	7
<b>E mm</b>	2,0
<b>F mm</b>	1,3
<b>A mm</b>	11
<b>Nominal size</b>	115 mm
<b>Length mm</b>	115
<b>Net weight g</b>	74



technical change and errors excepted

