

64 62 120 ESD

Electronics End Cutting Nippers ESD



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction hardened, cutting edge hardness at least 56 HRC
- With two-colour dual component grips, black/grey
- High-grade special tool steel, forged, multi stage oil-hardened
 - Style: Oblique End Cutter, mini-blade with small bevel, $\alpha = 65^\circ$




ESD pliers (electrostatic discharge)

electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

| | |
|--|----------------------------|
| Article No. | 64 62 120 ESD |
| EAN | 4003773025085 |
| Head | mirror polished |
| Handles | with multi-component grips |
| Style | 6 |
| Cutting capacities soft wire (diameter) Ø mm | 0,6 |
| B mm | 18,5 |
| D mm | 6,0 |
| C mm | 5,0 |
| A mm | 9,5 |
| Dimensions angle ° | 65 |
| Length mm | 120 |
| Net weight g | 70 |

 64 62 120 ESD

 64 62 120

technical change and errors excepted

