

# 67 01 160

## High Leverage End Cutting Nipper



- With cutting edges for soft, hard and piano wire
- High cutting capacity with little effort due to optimum co-ordination of cutting edge angle and transmission ratio
- Cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



Article No.	67 01 160
EAN	4003773040620
Pliers	black atramentized
Head	polished
Handles	plastic coated
Cutting capacities medium hard wire (diameter) Ø mm	3,4
Cutting capacities hard wire (diameter) Ø mm	2,5
Cutting capacities piano wire (diameter) Ø mm	2,0
Cutting capacities soft wire (diameter) Ø mm	4,5
Length mm	160
Net weight g	237



technical change and errors excepted

