

74 06 250

High Leverage Diagonal Cutter



- With integrated forged axle for heaviest duty
- Suitable for all types of wire including piano wire
- High cutting performance with minimum effort due to optimum co-ordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened
- The 250-mm-long diagonal cutter is suitable for copper conductors up to 16 mm² and aluminium conductors up to 35 mm²

20 % less effort required

compared to conventional diagonal cutters of the same length.

With integrated forged joint axle.

Article No.	74 06 250
EAN	4003773041955
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested
Style	0
Head	
Insulation standard	IEC 60900 DIN EN 60900
Cutting capacities medium hard wire (diameter) Ø mm	4,6
Cutting capacities hard wire (diameter) Ø mm	3,5
Cutting capacities piano wire (diameter) Ø mm	3,0
Length mm	250
Net weight g	453

technical change and errors excepted

