

74 22 250 T

High Leverage Diagonal Cutter with tether attachment point



- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened
 - Style: 25° angled handles offer clearance for gripping
- Pliers with tether attachment point for mounting a fall protection




20 % less effort required

compared to conventional diagonal cutters of the same length.

With integrated forged joint axle.

Article No.	74 22 250 T
EAN	4003773080114
Pliers	black atramentized
Head	polished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Style	2
Cutting capacities medium hard wire (diameter) Ø mm	4,6
Cutting capacities hard wire (diameter) Ø mm	3,5
Cutting capacities piano wire (diameter) Ø mm	3,0
Length mm	250
Net weight g	460



technical change and errors excepted