

77 32 120 H



Electronics Diagonal Cutter with inserted carbide metal cutting edges



- For extreme demands on cutting pliers caused by hard or tough materials, e.g. piano, nickel, tungsten and diode wire, such as those used more frequently in the electronics and aerospace industries
- Always the right cutting tool, even with the hardest material
- Precision carbide metal cutting edges soldered into forged blanks
- Sturdy, zero-backlash box joint
- Hardness of the carbide cutting edges 80 - 83 HRC
- Pliers with carbide metal cutting edges have a substantially longer service life than such with conventional cutting edges
- Constantly reliable cutting results due to the avoidance of cutter deformations
- High cost saving due to longer service life of the pliers
- Pointed head with chamfer
- With small bevel



Article No.	77 32 120 H
EAN	4003773075790
Head	mirror polished
Handles	with multi-component grips
Cutting capacities hard wire (diameter) Ø mm	0,6
Cutting capacities piano wire (diameter) Ø mm	0,2
Cutting capacities medium hard wire (diameter) Ø mm	1,0
Cutting capacities soft wire (diameter) Ø mm	1,6
B mm	14
D mm	7,5
A mm	11
Length mm	120
Net weight g	80



technical change and errors excepted

