

95 26 165


Cable Shears with opening spring



- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire and hard drawn copper conductors
- Precision ground, hardened blades
- Clean and smooth cut without crushing and deformation
- Easy cutting with one-hand operation
- Guard prevents operators' fingers being pinched
- Adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened
 - Style: internal opening spring, protected and captive




Article No.	95 26 165
EAN	4003773069980
Tool	chrome plated
Handles	insulated with multi-component grips, VDE-tested
Style	2
Insulation standard	IEC 60900 DIN EN 60900
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	15
Cutting capacity copper cable, multiple-stranded mm²	50
AWG	1/0
Length mm	165
Net weight g	275



Cut performed with a Diagonal Cutter: high effort required, inaccurate cut, considerable deforming and crushing of the cable



Cut performed with a Cable Shear: easy, clean cut without any deformation of the cable



95 26 165: Catch locks shears to the opening spring inside

technical change and errors excepted

