

Part Number: BE43802

RailTuff Cat 7, AWG 24 (19), Premium LSNH



Product Description

Railway approved Cat 7, High Flex, AWG 24 (19), Heavy Shielded, DIN 5510-2 level 1 to 4, EN 50155

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	Support current and future Cat. 6A and 7 applications for fixed installation in railway vehicles, support protocols such as 10GBase-T (10 Gigabit Ethernet), 1000Base-T (Gigabit Ethernet), 100 Base-T, 10 Base-T, FDDI, ATM

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	19x36	TC - Tinned Copper	4

Conductor Count:	8
Total Number of Pairs:	4
Conductor Size:	24 AWG

Insulation

Material
E-beam X-Linked Foam-skin polyethylene

Color Chart

Number	Color
Pair 1	White & Blue
Pair 2	White & Orange
Pair 3	White & Green
Pair 4	White & Brown

Inner Shield Material

Type	Material
Foil	Laminated aluminium / polyester

InnerShield, Table Note:	Aluminium facing outside
--------------------------	--------------------------

Outer Shield Material

Type	Material	Min. Coverage [%]
Braid	TC - Tinned Copper	80 %

Outer Jacket Material

Material	Color	Nominal Diameter	Diameter +/- Tolerance
E-beam X-LSZH / FRNC	Blue	8.1 mm	0.03 mm

Construction and Dimensions

Min Elongation at Breakof Conductors:	10 %
---------------------------------------	------

Cabling

Description
4 pairs twisted together

Min Elongation at Breakof Jacket:	125 %
Min Tensile Strength of Jacket:	10 MPa

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max DCR Unbalanced Between Pairs [%]	Max. DCR Unbalanced Within Pair [%]
95 Ohm/km	4 %	2 %

Capacitance

Max. Capacitance Unbalanced Pair to Pair	Max. Mutual Capacitance
1,600 pF/m	56 pF/m

Shielding:	SF/UTP - Overall Braid + Foil
------------	-------------------------------

Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
25 ns/100m	78 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)
1 MHz	2.9 dB/100m
4 MHz	5.6 dB/100m
10 MHz	8.8 dB/100m
16 MHz	11.1 dB/100m
31.2 MHz	15.6 dB/100m
62.5 MHz	22.3 dB/100m
100 MHz	28.5 dB/100m
300 MHz	51.3 dB/100m
600 MHz	75.1 dB/100m
1000 MHz	100.4 dB/100m

High Freq Table Note:	Limits below 4MHz are for information only. Values at 1000 MHz are for information only
Coupling Attenuation Table Note:	IEC 61156-5
Coupling Attenuation Class:	Type I
Transfer Impedance Table Note:	IEC 61156-5
Transfer Impedance Class:	Grade 1

Current

Max. Recommended Current [A]
1.5 A

Voltage

Voltage Rating [V]	Voltage Test Dielectric
300 V	2.0 kV DC

Temperature Range

Operating Temp Range:	-40°C To +80°C
Operating Temp Range (Flexible Install):	-5°C To +80°C

Mechanical Characteristics

Aging:	Pass EN 50290-2-29 and 50264-1
--------	--------------------------------

Standards

ISO/IEC Compliance:	ISO/IEC 11801 Ed. 2.2:2002/A2:2010/C1:2011
CENELEC Compliance:	EN 45545-2:2013, EN 50173-1 Ed. 3:2011
Data Category:	Category 7
Other Specification:	DIN 5510-2, LU 1-085 and ECE R118

Applicable Environmental and Other Programs

EU RoHS Compliance Date (yyyy-mm-dd):	2013-07-25
---------------------------------------	------------

Flammability, LS0H, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1-2 and IEC 60332-3-25 cat D
Other Flammability:	EN 50305 (9.1.1)
Amount of Halogen acc. to IEC 60754-1 & EN50267-1:	Zero

Part Number

Variants

Item #	Color
BE43802.00500	Blue
BE43802.01500	Blue

Patent:	https://www.belden.com/resources/patents
---------	---

History

Revision Number:	8
------------------	---

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.