

Crimp Information Sheet

Terminal Part Number: 15363934
 Surface Plating: SN
 Material Thickness [mm]: -
 Cross Section [mm²]: 0,50

*This document is non-contractual
 and for information only.
 For more information, please
 consult your local sales office*



Cable Type codes: 1005
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,60 - 1,88
 Seal(s): 15324974

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1005 0,50 / 15324974		1,74	80	1,10	0,05	2,00	0,10	3,80	0,10	4,10	0,10

Cable type code legend:

1005:

Industry Designator: SAE
 Conductor Material: COPPER
 Conductor Plating: NONE
 Insul. Material: PVC, PVDF, XLPE
 Insul. Wall Designator: THIN



Crimp Information Sheet

Terminal Part Number: 15363934
 Surface Plating: SN
 Material Thickness [mm]: -
 Cross Section [mm²]: 0,50 | 0,75 | 1,00

*This document is non-contractual
 and for information only.
 For more information, please
 consult your local sales office*



Cable Type codes: 2010
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,30 - 2,10
 Seal(s): 15324976 | 15324974

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 0,50 / 15324976		1,50	80	1,15	0,05	1,90	0,10	3,90	0,10	4,05	0,10
2010 0,50 / 15324974		1,50	80	1,15	0,05	1,90	0,10	3,70	0,10	4,05	0,10
2010 0,75 / 15324976		1,75	120	1,25	0,05	1,90	0,10	4,00	0,10	4,05	0,10
2010 1,00 / 15324976		1,95	160	1,35	0,05	1,95	0,10	4,10	0,10	4,05	0,10
2010 1,00 / 15324974		1,95	160	1,35	0,05	1,95	0,10	3,90	0,10	4,05	0,10

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR (AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B

Industry Designator: DIN
 Conductor Material: COPPER
 Conductor Plating: NONE
 Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE, XLPE/PVDF, XLPVC
 Insul. Wall Designator: THIN



Crimp Information Sheet

Terminal Part Number: 15363934
 Surface Plating: SN
 Material Thickness [mm]: -
 Cross Section [mm²]: 0,75

*This document is non-contractual
 and for information only.*



*For more information, please
 consult your local sales office*

Cable Type codes: 2023
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 2,20 - 2,50
 Seal(s): 15324973

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2023 0,75 / 15324973		2,35	120	1,25	0,05	1,90	0,10	4,20	0,10	4,10	0,10

Cable type code legend:

2023: FL2G
 Industry Designator: DIN
 Conductor Material: COPPER
 Conductor Plating: SN
 Insul. Material: SIL, SIR
 Insul. Wall Designator: REGULAR



Crimp Information Sheet

Terminal Part Number: 15363934
 Surface Plating: SN
 Material Thickness [mm]: -
 Cross Section [mm²]: 0,50 | 0,75 | 1,00 | 1,40



*This document is non-contractual
 and for information only.
 For more information, please
 consult your local sales office*

Cable Type codes: 2044
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,40 - 2,40
 Seal(s): 15324974 | 15324973

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2044 0,50 / 15324974		1,50	80	1,15	0,05	1,90	0,10	3,70	0,10	4,05	0,10
2044 0,75 / 15324974		1,78	120	1,25	0,05	1,90	0,10	3,80	0,10	4,05	0,10
2044 1,00 / 15324974		1,96	160	1,35	0,05	1,95	0,10	3,90	0,10	4,05	0,10
2044 1,40 / 15324973		2,30	120	1,30	0,05	2,25	0,10	3,90	0,10	4,20	0,10

Cable type code legend:

2044: A3Z, F3Z, FL RENAULT A3Z
 Industry Designator: NRA
 Conductor Material: COPPER
 Conductor Plating: NONE
 Insul. Material: XLPA/PVDF, XLPE, X-POLY ZH
 Insul. Wall Designator: THIN



Crimp Information Sheet

Terminal Part Number: 15363934
 Surface Plating: SN
 Material Thickness [mm]: -
 Cross Section [mm²]: 0,50 | 0,75 | 1,00



*This document is non-contractual
 and for information only.
 For more information, please
 consult your local sales office*

Cable Type codes: 2055
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,40 - 2,10
 Seal(s): 15324974

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2055 0,50 / 15324974		1,50	80	1,15	0,05	1,90	0,10	3,80	0,10	4,10	0,10
2055 0,75 / 15324974		1,70	120	1,25	0,05	1,90	0,10	3,90	0,10	4,10	0,10
2055 1,00 / 15324974		1,93	160	1,35	0,05	1,90	0,10	4,00	0,10	4,10	0,10

Cable type code legend:

2055: AGP0119, RENAULT F3Z
 Industry Designator: NRA
 Conductor Material: COPPER
 Conductor Plating: NONE
 Insul. Material: POLYOLEFIN
 Insul. Wall Designator: THIN



Crimp Information Sheet

Terminal Part Number: 15363934
 Surface Plating: SN
 Material Thickness [mm]: -
 Cross Section [mm²]: 0,50

*This document is non-contractual
 and for information only.
 For more information, please
 consult your local sales office*



Cable Type codes: 2083
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,40 - 1,70
 Seal(s): 15324974

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2083 0,50 / 15324974		1,55	75	1,10	0,05	2,00	0,10	3,80	0,10	4,10	0,10

Cable type code legend:

2083:

Industry Designator: ISO
 Conductor Material: COPPER
 Conductor Plating: NONE
 Insul. Material: PVC (YW)
 Insul. Wall Designator: THIN



Crimp Information Sheet

Terminal Part Number: 15363934
 Surface Plating: SN
 Material Thickness [mm]: -
 Cross Section [mm²]: 0,50

*This document is non-contractual
 and for information only.
 For more information, please
 consult your local sales office*

Cable Type codes: 3004
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,50 - 1,70
 Seal(s): 15324974

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
3004 0,50 / 15324974		1,60	75	1,05	0,05	2,05	0,10	3,70	0,10	4,10	0,10

Cable type code legend:

3004: AVSS
 Industry Designator: JIS/JA
 Conductor Material: COPPER
 Conductor Plating: NONE
 Insul. Material: PVC, XLPE, X-PVC
 Insul. Wall Designator: THIN

