

product: DELPHI PN 15344717

material: CUZN9SN3

VERSION I

surface: F.SN3

material thickness: 0,32 mm

cross section [mm²]: 1,5 | 2,5

strip length: 4,60 mm

cable type: FLRY-B

insulation ø [mm]: 2,20 - 3,00

seal: DPN 15363980

**Uncontrolled
Copy
For Information only!**


conductor dimension					crimp dimension [mm]					
cable type	cross sect. [mm ²]	struct. n x d [mm]	insul. diam. [mm]	tear-out force [N]	core		insulation			
					height ± 0,05	width ± 0,10	height ± 0,10	width ± 0,10	height ± tol.	width ± tol.
FLRY-B	1,5	30 x 0,26	2,30	200	1,50	2,55	4,50	5,00		
FLRY-B	2,5	50 x 0,26	2,85	250	1,70	2,60	4,70	5,10		

core:
C-2.50-3.5-19
DPN 10713724


insulation:
IS-5.00-3.0-19-X GD 66,0
DPN 10713814

anvil:
ASR-2.50-5.00-8.0-2.8-1.0
DPN 10714088

two piece anvil:
AC-2.50-3.75
DPN 10769936
AI-5.00-4.2-1.0
DPN 10807118




DELPHI PN 15344717



cable:
 $1,50 \text{ mm}^2 = 30 \times 0,26 \text{ mm}$

crimp height:
1,50 mm

crimp width:
2,55 mm



cable:
 $2,50 \text{ mm}^2 = 50 \times 0,26 \text{ mm}$

crimp height:
1,70 mm

crimp width:
2,60 mm