

# PRO-POWER

## SAFETY DATA SHEET according to Regulation (EU) 2015/830

Page 1/7

### Pro Power Screen Wash -5

Revision 1  
Revision date 10-10-2018

#### SECTION 1: Identification of the substance/mixture and of the company/undertaking

##### 1.1. Product identifier

Product name	Pro Power Screen Wash -5
--------------	--------------------------

##### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Product Use	[SU21] Consumer uses: Private households (= general public = consumers); ----- [SU22] Professional uses: Public domain (administration, education, entertainment, services, craftsmen);
Description	Screen Wash.

##### 1.3. Details of the supplier of the safety data sheet

Company Address	<b>CPC Component House Faraday Drive Fulwood, Preston Lancashire PR2 9PP</b>
Web	www.CPC.co.uk
Telephone	03447 880088
Email	sales@cpc.co.uk
Email address of the competent person	productinfo@cpc.co.uk

##### 1.4. Emergency telephone number


Emergency telephone number	03447 880088
----------------------------	--------------

#### SECTION 2: Hazards identification

##### 2.1. Classification of the substance or mixture

2.1.2. Classification - EC 1272/2008	Flam. Liq. 3: H226; Acute Tox. 4: H332; STOT SE 1: H370;
--------------------------------------	--

##### 2.2. Label elements

Hazard pictograms	
Signal Word	Danger
Hazard Statement	Flam. Liq. 3: H226 - Flammable liquid and vapour. Acute Tox. 4: H332 - Harmful if inhaled. STOT SE 1: H370 - Causes damage to organs .

## Pro Power Screen Wash -5

Revision 1

Revision date 10-10-2018

## 2.2. Label elements

<b>Precautionary Statement: Prevention</b>	<p>P102 - Keep out of reach of children</p> <p>P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.</p> <p>P233 - Keep container tightly closed.</p> <p>P240 - Ground/bond container and receiving equipment.</p> <p>P241 - Use explosion-proof electrical/ventilating/lighting// equipment.</p> <p>P242 - Use only non-sparking tools.</p> <p>P243 - Take precautionary measures against static discharge.</p> <p>P260 - Do not breathe dust/fume/gas/mist/vapours/spray.</p> <p>P261 - Avoid breathing dust/fume/gas/mist/vapours/spray.</p> <p>P264 - Wash thoroughly after handling.</p> <p>P270 - Do not eat, drink or smoke when using this product.</p> <p>P271 - Use only outdoors or in a well-ventilated area.</p> <p>P280 - Wear protective gloves/protective clothing/eye protection/face protection.</p>
<b>Precautionary Statement: Response</b>	<p>P303+P361+P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.</p> <p>P304+P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing.</p> <p>P312 - Call a POISON CENTER/doctor/ if you feel unwell.</p> <p>P321 - Specific treatment (see on this label).</p> <p>P370+P378 - In case of fire: Use to extinguish.</p>
<b>Precautionary Statement: Storage</b>	<p>P403+P235 - Store in a well-ventilated place. Keep cool.</p> <p>P405 - Store locked up.</p>
<b>Precautionary Statement: Disposal</b>	<p>P501 - Dispose of contents/container to local and national regulations</p>

## SECTION 3: Composition/information on ingredients

## 3.2. Mixtures

## EC 1272/2008

Chemical Name	Index No.	CAS No.	EC No.	REACH Registration Number	Conc. (%w/w)	Classification
Methanol	603-001-00-X	67-56-1	200-659-6		1 - 10%	Flam. Liq. 2: H225; Acute Tox. 3: H331; Acute Tox. 3: H311; Acute Tox. 3: H301; STOT SE 1: H370;

## SECTION 4: First aid measures

## 4.1. Description of first aid measures

<b>Inhalation</b>	Harmful by inhalation. Inhalation may cause nausea and vomiting. May cause dizziness and headache. Move the exposed person to fresh air. Seek medical attention.
<b>Eye contact</b>	May cause irritation to eyes. Rinse immediately with plenty of water for 15 minutes holding the eyelids open. Seek medical attention if irritation or symptoms persist.
<b>Skin contact</b>	May cause irritation to skin. May cause dermatitis. Wash off immediately with plenty of soap and water. Remove contaminated clothing. Seek medical attention if irritation or symptoms persist.
<b>Ingestion</b>	Harmful if swallowed. Ingestion may cause nausea and vomiting. Ingestion is irritating to the respiratory tract and may cause damage to the central nervous system. DO NOT INDUCE VOMITING. If swallowed, seek medical advice immediately and show this container or label.

## 4.2. Most important symptoms and effects, both acute and delayed

<b>Inhalation</b>	See section 4.1 for further information.
<b>Eye contact</b>	See section 4.1 for further information.
<b>Skin contact</b>	See section 4.1 for further information.
<b>Ingestion</b>	See section 4.1 for further information.

## 4.3. Indication of any immediate medical attention and special treatment needed

# Pro Power Screen Wash -5

Revision 1  
Revision date 10-10-2018

## 4.3. Indication of any immediate medical attention and special treatment needed

If you feel unwell, seek medical advice (show the label where possible). No further relevant information available.

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

### 5.2. Special hazards arising from the substance or mixture

Burning produces irritating, toxic and obnoxious fumes.

### 5.3. Advice for firefighters

Wear suitable respiratory equipment when necessary.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation of the working area. Eliminate all sources of ignition. Wear suitable protective equipment.

### 6.2. Environmental precautions

Do not allow product to enter drains. Prevent further spillage if safe.

### 6.3. Methods and material for containment and cleaning up

Absorb with inert, absorbent material. Transfer to suitable, labelled containers for disposal. Clean spillage area thoroughly with plenty of water.

### 6.4. Reference to other sections

See section 2,3,8,13 for further information.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Avoid contact with eyes and skin. Ensure adequate ventilation of the working area. Use explosion proof equipment. Keep away from sources of ignition - No smoking. Adopt best Manual Handling considerations when handling, carrying and dispensing.

### 7.2. Conditions for safe storage, including any incompatibilities

Keep in a cool, dry, well ventilated area. Keep containers tightly closed.

### 7.3. Specific end use(s)

See section 1.2 for further information.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

See section 8.2 for further information.

#### 8.1.1. Exposure Limit Values



Methanol	WEL 8-hr limit ppm:	200	WEL 8-hr limit mg/m3:	266
	WEL 15 min limit ppm:	250	WEL 15 min limit mg/m3:	333
	WEL 8-hr limit mg/m3 total	-	WEL 15 min limit mg/m3 total	-
	inhalable dust:		inhalable dust:	
	WEL 8-hr limit mg/m3 total	-	WEL 15 min limit mg/m3 total	-
	respirable dust:		respirable dust:	

### 8.2. Exposure controls

## Pro Power Screen Wash -5

Revision 1  
Revision date 10-10-2018

## 8.2. Exposure controls

	 
8.2.1. Appropriate engineering controls	Ensure adequate ventilation of the working area.
8.2.2. Individual protection measures	Wear chemical protective clothing.
Eye / face protection	Approved safety goggles.
Skin protection - Handprotection	Chemical resistant gloves (PVC).

## SECTION 9: Physical and chemical properties

## 9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Various
Odour	Characteristic
pH	7 - 8
Melting point	Not applicable.
Freezing Point	-5 °C
Initial boiling point	Not applicable.
Flash point	60 °C
Flammability (solid, gas)	Not applicable.
Fat Solubility	Not applicable.
Partition coefficient	Not applicable.
Autoignition temperature	Not applicable.
Viscosity	Not applicable.
Explosive properties	Not applicable.
Oxidising properties	Not applicable.
Solubility	Soluble in water

## 9.2. Other information

Conductivity	Not applicable.
Surface tension	Not applicable.

## SECTION 10: Stability and reactivity

## 10.1. Reactivity

	No hazardous reactions when stored and handled as indicated.
--	--

## 10.2. Chemical stability

	Stable under normal conditions.
--	---------------------------------

## 10.3. Possibility of hazardous reactions

	No data is available on this product.
--	---------------------------------------

## 10.4. Conditions to avoid

	No data is available on this product.
--	---------------------------------------

## 10.5. Incompatible materials

	No data available.
--	--------------------

## 10.6. Hazardous decomposition products

--	--

## Pro Power Screen Wash -5

Revision 1  
Revision date 10-10-2018

## 10.6. Hazardous decomposition products

No data is available on this product.

**SECTION 11: Toxicological information**

## 11.1. Information on toxicological effects

Acute toxicity	Harmful if swallowed.
Skin corrosion/irritation	Harmful in contact with skin.
Respiratory or skin sensitisation	May be harmful if inhaled.

## 11.1.4. Toxicological Information

No data available

**SECTION 12: Ecological information**

## 12.1. Toxicity

No data available

## 12.2. Persistence and degradability

No data is available on this product.

## 12.3. Bioaccumulative potential

No data is available on this product.

## Partition coefficient

Pro Power Screen Wash -5 Not applicable.

## 12.4. Mobility in soil

No data is available on this product.

## 12.5. Results of PBT and vPvB assessment

No data is available on this product.

## 12.6. Other adverse effects

However, large or frequent spills may have hazardous effects on the environment. The product is not regarded as dangerous for the environment.

**SECTION 13: Disposal considerations**

## 13.1. Waste treatment methods

Must be disposed of in accordance with local and national regulations.

## General information

Dispose of in compliance with all local and national regulations.

**SECTION 14: Transport information**

## Hazard pictograms



## 14.1. UN number

UN1993

## 14.2. UN proper shipping name

## Pro Power Screen Wash -5

Revision 1

Revision date 10-10-2018

## 14.2. UN proper shipping name

	FLAMMABLE LIQUID, N.O.S.
--	--------------------------

## 14.3. Transport hazard class(es)

ADR/RID	3
Subsidiary risk	-
IMDG	3
Subsidiary risk	-
IATA	3
Subsidiary risk	-

## 14.4. Packing group

Packing group	III
---------------	-----

## 14.5. Environmental hazards

Environmental hazards	No
Marine pollutant	No

## ADR/RID

Hazard ID	30
Tunnel Category	(D/E)

## IMDG

EmS Code	F-E S-E
----------	---------

## IATA

Packing Instruction (Cargo)	366
Maximum quantity	220 L
Packing Instruction (Passenger)	355
Maximum quantity	60 L

## SECTION 15: Regulatory information

## 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

	The classification detailed on this safety data sheet refers to the neat material only. Dilution of the product may reduce the classification. This safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006 & (EC) No. 1272/2008 & (EC) 1999/45.
--	--

## 15.2. Chemical safety assessment

	No further relevant information available.
--	--

## SECTION 16: Other information

## Other information

Revision	This document differs from the previous version in the following areas: 2 - 2.1.2. Classification - EC 1272/2008.
Text of Hazard Statements in Section 3	Flam. Liq. 2: H225 - Highly flammable liquid and vapour. Acute Tox. 3: H301 - Toxic if swallowed. Acute Tox. 3: H311 - Toxic in contact with skin. Acute Tox. 3: H331 - Toxic if inhaled. STOT SE 1: H370 - Causes damage to organs . STOT SE 2: H371 - May cause damage to organs .

## Further information

	The information supplied in this Safety Data Sheet is designed only as guidance for the safe use, storage and handling of the product. This information is correct to the best of our knowledge and belief at the date of publication however no guarantee is made to its accuracy. This information
--	--

# Pro Power Screen Wash -5

Revision 1

Revision date 10-10-2018

---

**Further information**

	relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any other process.
--	---

---