

TECHNICAL DATA SHEET

PRO-POWER

Telephone Cable Model: 9102 4PRCCS

**RoHS
Compliant**

Design of cable:	
Inner conductor	Single copper steel $\varnothing 0.48 \pm 0.01 \text{mm}$
Insulation	PVC
Insulation Dia	$\varnothing 0.91 \pm 0.05 \text{mm}$
Colour	WH/BU WH/OG WH/GN WH/BN
Jacket	PVC
Size	$\varnothing 5.1 \pm 0.5 \text{mm}$
Wall thickness	$\approx 0.5 \text{mm}$
Printing	By request
Electric data at 20°C	
Conductor resistance	$\leq 650 \text{ Ohm/km}$
Insulation resistance	$\geq 200 \text{M}\Omega \cdot \text{km}$
Testing voltage	wire/wire/screen 50Hz 1min=800V
Other requirements	
Permissible temperature	-10°C---60°C
Packing	100M on non-returnable reel

Important Notice : This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

PRO-POWER