

Part Details:-

Part Number	Description
MKV250V-KIT-4-DE	250V TO 1000V CAPACITORS FOR OUTPUT SMOOTHING

KIT Contents:-

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Remarks	Qty
1	GRM31AR72J102KW01	3216M/1206	X7R	630Vdc	1000pF	±10%	1.0max		10
2	GRM31AR72J152KW01	3216M/1206	X7R	630Vdc	1500pF	±10%	1.0max		10
3	GRM31AR72J222KW01	3216M/1206	X7R	630Vdc	2200pF	±10%	1.0max		10
4	GRM31AR72J332KW01	3216M/1206	X7R	630Vdc	3300pF	±10%	1.0max		10
5	GRM31AR72J472KW01	3216M/1206	X7R	630Vdc	4700pF	±10%	1.0max		10
6	GRM31BR73A102KW01	3216M/1206	X7R	1KVdc	1000pF	±10%	1.25max		10
7	GRM31BR73A152KW01	3216M/1206	X7R	1KVdc	1500pF	±10%	1.25max		10
8	GRM31BR73A222KW01	3216M/1206	X7R	1KVdc	2200pF	±10%	1.25max		10
9	GRM31BR73A332KW01	3216M/1206	X7R	1KVdc	3300pF	±10%	1.25max		10
10	GRM31BR73A472KW01	3216M/1206	X7R	1KVdc	4700pF	±10%	1.25max		10
11	GRM31A5C2J101JW01	3216M/1206	C0G	630Vdc	100pF	±5%	1.0max		10
12	GRM31A5C2J151JW01	3216M/1206	C0G	630Vdc	150pF	±5%	1.0max		10
13	GRM31A5C2J221JW01	3216M/1206	C0G	630Vdc	220pF	±5%	1.0max		10
14	GRM31A5C2J331JW01	3216M/1206	C0G	630Vdc	330pF	±5%	1.0max		10
15	GRM31A5C2J471JW01	3216M/1206	C0G	630Vdc	470pF	±5%	1.0max		10
16	GRM31B5C2J681JW01	3216M/1206	C0G	630Vdc	680pF	±5%	1.25max		10
17	GRM31B5C2J102JW01	3216M/1206	C0G	630Vdc	1000pF	±5%	1.25max		10
18	GRM31A5C3A101JW01	3216M/1206	C0G	1KVdc	100pF	±5%	1.0max		10
19	GRM31A5C3A151JW01	3216M/1206	C0G	1KVdc	150pF	±5%	1.0max		10
20	GRM31A5C3A221JW01	3216M/1206	C0G	1KVdc	220pF	±5%	1.0max		10
21	GRM31A7U2J101JW31	3216M/1206	U2J	630Vdc	100pF	±5%	1.0max		10
22	GRM31A7U2J102JW31	3216M/1206	U2J	630Vdc	1000pF	±5%	1.0max		10
23	GRM31A7U2J151JW31	3216M/1206	U2J	630Vdc	150pF	±5%	1.0max		10
24	GRM31A7U2J221JW31	3216M/1206	U2J	630Vdc	220pF	±5%	1.0max		10
25	GRM31A7U2J331JW31	3216M/1206	U2J	630Vdc	330pF	±5%	1.0max		10
26	GRM31A7U2J471JW31	3216M/1206	U2J	630Vdc	470pF	±5%	1.0max		10
27	GRM31A7U2J681JW31	3216M/1206	U2J	630Vdc	680pF	±5%	1.0max		10
28	GRM31A7U3A101JW31	3216M/1206	U2J	1KVdc	100pF	±5%	1.0max		10
29	GRM31A7U3A151JW31	3216M/1206	U2J	1KVdc	150pF	±5%	1.0max		10
30	GRM31A7U3A221JW31	3216M/1206	U2J	1KVdc	220pF	±5%	1.0max		10
31	GRM31A7U3A331JW31	3216M/1206	U2J	1KVdc	330pF	±5%	1.0max		10
32	GRM31B7U3A471JW31	3216M/1206	U2J	1KVdc	470pF	±5%	1.25max		10
33	GRM31B7U3A681JW31	3216M/1206	U2J	1KVdc	680pF	±5%	1.25max		10

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Remarks	Qty
34	GRM31C7U3A102JW32	3216M/1206	U2J	1KVdc	1000pF	±5%	1.8max		10
35	RDER72J102K2K1H03	-	X7R	250Vdc	1000pF	±10%	-		10
36	RDER72J152K2K1H03	-	X7R	250Vdc	1500pF	±10%	-		10
37	RDER72J222K2K1H03	-	X7R	250Vdc	2200pF	±10%	-		10
38	RDER72J332K2K1H03	-	X7R	250Vdc	3300pF	±10%	-		10
39	RDER72J472K2K1H03	-	X7R	250Vdc	4700pF	±10%	-		10
40	RDER73A102K2K1H03	-	X7R	250Vdc	1000pF	±10%	-		10
41	RDER73A152K2K1H03	-	X7R	250Vdc	1500pF	±10%	-		10
42	RDER73A222K2K1H03	-	X7R	250Vdc	2200pF	±10%	-		10
43	RDER73A332K2K1H03	-	X7R	250Vdc	3300pF	±10%	-		10
44	RDER73A472K2K1H03	-	X7R	250Vdc	4700pF	±10%	-		10
45	RDE7U2J101J2K1H03	-	U2J	250Vdc	100pF	±5%	-		10
46	RDE7U2J151J2K1H03	-	U2J	250Vdc	150pF	±5%	-		10
47	RDE7U2J221J2K1H03	-	U2J	250Vdc	220pF	±5%	-		10
48	RDE7U2J331J2K1H03	-	U2J	250Vdc	330pF	±5%	-		10
49	RDE7U2J471J2K1H03	-	U2J	250Vdc	470pF	±5%	-		10
50	RDE7U2J681J2K1H03	-	U2J	250Vdc	680pF	±5%	-		10
51	RDE7U2J102J2K1H03	-	U2J	250Vdc	1000pF	±5%	-		10
52	RDE7U3A101J2K1H03	-	U2J	250Vdc	100pF	±5%	-		10
53	RDE7U3A151J2K1H03	-	U2J	250Vdc	150pF	±5%	-		10
54	RDE7U3A221J2K1H03	-	U2J	250Vdc	220pF	±5%	-		10
55	RDE7U3A331J2K1H03	-	U2J	250Vdc	330pF	±5%	-		10
56	RDE7U3A471J2K1H03	-	U2J	250Vdc	470pF	±5%	-		10
57	RDE7U3A681J2K1H03	-	U2J	250Vdc	680pF	±5%	-		10
58	RDE7U3A102J2K1H03	-	U2J	250Vdc	1000pF	±5%	-		10